

35 ft 10m Plenum-Rated Coax High Resolution Monitor / Projector VGA Cable - HD15 to HD15 M/M

Product ID: MXT101PMM35



The MXT101PMM35 35 ft long plenum-rated VGA cable allows for connection distances of up to 35 feet to your monitor or projector and can be installed through air plenums, ducts, walls, conduits, ceilings, or anywhere else a CMP/FT6 fire rating is required.

This durably constructed coaxial cable features two HD15 (male) connectors and eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial cables, while providing superior EMI interference protection by using ferrite cores near the connector ends.

This 35-foot plenum-rated VGA cable is backed by StarTech.com's Lifetime Warranty.

Certifications, Reports and Compatibility



Applications

- VGA display installations where cable needs to be run through air ducts and plenums, where CMP fire rating is required (educational or commercial installations, etc.)
- Connect a high resolution display to a Desktop PC or video switch, up to 35 feet away

Features

- CMP/FT6 Plenum Fire Rating

- 2x VGA HD15 male connectors
- Triple coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief
- Supports high resolution VGA monitors (1920x1200 and above)

Hardware

| | |
|-----------------------|--------------------------------|
| Warranty | Lifetime |
| Number of Conductors | 14 |
| Connector Plating | Nickel |
| Cable Jacket Material | PVC - Polyvinyl Chloride |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Fire Rating | CMP Rated (Plenum) |

Performance

| | |
|-----------|--------|
| Impedance | 75 Ohm |
|-----------|--------|

Connector(s)

| | |
|-------------|--------------------------------------|
| Connector A | 1 - VGA (15 pin, High Density D-Sub) |
| Connector B | 1 - VGA (15 pin, High Density D-Sub) |

Physical Characteristics

| | |
|-------------------|------------------|
| Color | Black |
| Connector Style | Straight |
| Wire Gauge | 28 AWG |
| Cable Length | 35.0 ft [10.7 m] |
| Product Length | 35.0 ft [10.7 m] |
| Product Width | 1.2 in [3.0 cm] |
| Product Height | 0.6 in [1.5 cm] |
| Weight of Product | 2.1 lb [1.0 kg] |

Packaging Information

| | |
|---------------------------|-------------------|
| Package Quantity | 1 |
| Package Length | 18.5 in [47.0 cm] |
| Package Width | 13.8 in [35.0 cm] |
| Package Height | 1.0 in [2.5 cm] |
| Shipping (Package) Weight | 2.2 lb [1.0 kg] |

What's in the Box

| | |
|---------------------|---|
| Included in Package | 1 - 35ft Plenum-Rated Coax VGA Monitor Cable HDDB15 M/M |
|---------------------|---|

**Product appearance and specifications are subject to change without notice.*