

15 ft Coax VGA Monitor Extension Cable - HD15 M/F

N° de produit: MXT105HQ



This 15ft High Resolution VGA Monitor Extension Cable is designed to provide the highest VGA video quality possible. Ideally suited for high resolution VGA applications (1024x768 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables and provides superior EMI interference protection by using ferrite cores near the connector ends.

A reliable solution for a wide range of applications, including connecting StarView KVM Switches, this high resolution VGA (SVGA) extension cable features one hddb15 male connector and one hddb15 female connector, offering a convenient way to extend a VGA or SVGA connection by up to 15ft, while maintaining superb image quality.

Certifications, rapports et compatibilité



Applications

- Extends VGA/SVGA monitor cable
- Connects PC's VGA port to a StarView

Spécifications techniques

- Triple-coaxial + twisted-pair wire for crystal clear display
- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference
- Impedence matched at 75 Ohms for full brightness and vibrant picture color
- Ideal for high resolution monitors (1024x768 and above)

Matériel

Politique de garantie	Lifetime
Placage du connecteur	Nickel

Connecteur(s)

Connecteur A	1 - VGA (15 broches , D-Sub haute densité)
Connecteur B	1 - VGA (15 broches , D-Sub haute densité)

Caractéristiques physiques

Couleur	Gris
Longueur de câble	15.0 ft [4.6 m]
Dia. ext. du câble	0.3 in [8.8 mm]
Longueur du produit	15.0 ft [4.6 m]
Largeur du produit	1.3 in [3.4 cm]
Hauteur du produit	0.6 in [1.5 cm]
Poids du produit	1.2 lb [0.5 kg]

Informations d'emballage

Quantité par paquet	1
Longueur du Paquet	6.8 in [17.3 cm]
Largeur du Paquet	7.8 in [19.8 cm]
Hauteur du Paquet	2.1 in [5.4 cm]

Poids brut	1.1 lb [0.5 kg]
------------	-----------------

Contenu du paquet

Inclus dans le paquet	1 - 15 FT COAXIAL SVGA CABLE
	2 - Nuts

Informations de
garantie

Warranty	À Vie
----------	-------

* L'apparence et les spécifications du produit peuvent être modifiées sans préavis