

15 ft Coax VGA Monitor Extension Cable - HD15 M/F

ID prodotto: MXT105HQ



This 15ft High Resolution VGA Monitor Extension Cable is designed to provide the highest VGA video quality possible. Ideally suited for high resolution VGA applications (1024x768 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables and provides superior EMI interference protection by using ferrite cores near the connector ends.

A reliable solution for a wide range of applications, including connecting StarView KVM Switches, this high resolution VGA (SVGA) extension cable features one hddb15 male connector and one hddb15 female connector, offering a convenient way to extend a VGA or SVGA connection by up to 15ft, while maintaining superb image quality.

Certificazioni, report e compatibilità

Applicazioni

- Extends VGA/SVGA monitor cable
- Connects PC's VGA port to a StarView

Caratteristiche

- Ideal for high resolution monitors (1024x768 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display

- Impedence matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference
- Molded connector ends with strain relief

Hardware

Norme di garanzia	Lifetime
Placcatura connettori	Nichel

Connettore/i

Connettore A	VGA (15 pin, D-Sub ad alta densità)
Connettore B	VGA (15 pin, D-Sub ad alta densità)

Caratteristiche fisiche

Colore	Grigio
Lunghezza cavo	15.0 ft [4.6 m]
Lunghezza prodotto	15.0 ft [4.6 m]
Larghezza prodotto	1.3 in [33.8 mm]
Altezza prodotto	0.6 in [15.1 mm]
Peso prodotto	19.0 oz [538 g]

Informazioni confezione

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	2.0 in [50 mm]
Peso spedizione (confezione)	19.4 oz [550 g]

Contenuto della confezione

Incluso nella confezione	15 FT COAXIAL SVGA CABLE
--------------------------	--------------------------



Nuts

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.

