

15 ft Coax VGA Monitor Extension Cable - HD15 M/F

Produkt ID: MXT105HQ



This 15ft High Resolution VGA Monitor Extension Cable is designed to provide the highest VGA video quality possible. Ideally suited for high resolution VGA applications (1024x768 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables and provides superior EMI interference protection by using ferrite cores near the connector ends.

A reliable solution for a wide range of applications, including connecting StarView KVM Switches, this high resolution VGA (SVGA) extension cable features one hddb15 male connector and one hddb15 female connector, offering a convenient way to extend a VGA or SVGA connection by up to 15ft, while maintaining superb image quality.

Certifikat, rapporter och kompatibilitet



Användning

- Extends VGA/SVGA monitor cable
- Connects PC's VGA port to a StarView

Funktioner

- Triple-coaxial + twisted-pair wire for crystal clear display
- Molded connector ends with strain relief
- Ferrite core eliminates EMI interference
- Impedence matched at 75 Ohms for full brightness and vibrant picture color
- Ideal for high resolution monitors (1024x768 and above)

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel

Kontakt(er)

Connector A	1 - VGA (15-stifts, High Density D-Sub)
Connector B	1 - VGA (15-stifts, High Density D-Sub)

Utseende

Färg	Grå
Kabellängd	15.0 ft [4.6 m]
Yttre kabeldiameter	0.3 in [8.8 mm]
Produktlängd	15.0 ft [4.6 m]
Produktbredd	1.3 in [3.4 cm]
Produkthöjd	0.6 in [1.5 cm]
Produktvikt	1.2 lb [0.5 kg]

Förpackning

Förpackningsantal	1
Paketets längd	6.8 in [17.3 cm]
Paketets bredd	7.8 in [19.8 cm]
Paketets höjd	2.1 in [5.4 cm]
Fraktvikt (förpackning)	1.1 lb [0.5 kg]

Vad det är i lådan

Ingår i paketet	1 - 15 FT COAXIAL SVGA CABLE
	2 - Nuts

Warranty
Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.