

15 ft Coax VGA Monitor Extension Cable - HD15 M/F

Product ID: MXT105HQ



This 15ft High Resolution VGA Monitor Extension Cable is designed to provide the highest VGA video quality possible. Ideally suited for high resolution VGA applications (1024x768 and above), this high quality coaxial VGA cable eliminates picture "ghosting" and fuzzy images inherent to non-coaxial cables and provides superior EMI interference protection by using ferrite cores near the connector ends.

A reliable solution for a wide range of applications, including connecting StarView KVM Switches, this high resolution VGA (SVGA) extension cable features one hddb15 male connector and one hddb15 female connector, offering a convenient way to extend a VGA or SVGA connection by up to 15ft, while maintaining superb image quality.

Certifications, Reports and Compatibility

Applications

- Extends VGA/SVGA monitor cable
- Connects PC's VGA port to a StarView

Features

- Ideal for high resolution monitors (1024x768 and above)
- Triple-coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Ferrite core eliminates EMI interference

- Molded connector ends with strain relief

Hardware

Warranty	Lifetime
Connector Plating	Nickel

Connector(s)

Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Gray
Cable Length	15.0 ft [4.6 m]
Product Length	15.0 ft [4.6 m]
Product Width	1.3 in [33.8 mm]
Product Height	0.6 in [15.1 mm]
Weight of Product	19.0 oz [538 g]

Packaging Information

Package Length	8.7 in [22 cm]
Package Width	7.9 in [20 cm]
Package Height	2.0 in [50 mm]
Shipping (Package) Weight	19.4 oz [550 g]

What's in the Box

Included in Package	15 FT COAXIAL SVGA CABLE
	Nuts

**Product appearance and specifications are subject to change without notice.*

