

10m Coax High Resolution Monitor VGA Video Extension Cable - HD15 M/F

Product ID: MXTHQ10M



The MXTHQ10M High Resolution VGA Extension Cable (10-meter) is designed to extend your VGA video connection while maintaining the highest video quality possible through VGA.

Ideally suited for high resolution VGA video applications, this high quality coaxial VGA extension cable (HD15 to HD15, M-F) helps eliminate the picture ghosting and fuzzy images that are inherent to non-coaxial cables, and features ferrite cores near the VGA connector ends to protect against EMI interference.

Certifications, Reports and Compatibility

Applications

- Extend your SVGA/VGA cable, for more convenient monitor placement
- Extend the connection distance between monitors, video splitters, projectors and a VGA video source

Features

- Triple coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- Ferrite cores to help eliminate EMI interference
- High quality VGA connectors with molded PVC strain relief
- Durably constructed cable, with high quality HD15 connectors

Connector(s)

Warranty	Lifetime
Connector A	VGA (15 pin, High Density D-Sub)
Connector B	VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	32.8 ft [10 m]
Product Length	32.8 ft [10 m]
Weight of Product	33.8 oz [957 g]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33 cm]
Package Width	10.0 in [25.5 cm]
Package Height	1.9 in [49 mm]
Shipping (Package) Weight	34.4 oz [975 g]

What's in the Box

Included in Package	10m Coax High Resolution VGA Monitor Extension Cable - HD15 M/F
	Nuts

**Product appearance and specifications are subject to change without notice.*

