

1m Coax High Resolution Monitor VGA Cable - HD15 M/M

Produkt ID: MXTMMHQ1M



The MXTMMHQ1M High Resolution VGA Cable (1-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifikat, rapporter och kompatibilitet

Användning

- Supports high resolution VGA monitors (1920x1200)
- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable

Funktioner

- Triple coaxial + twisted-pair wire for crystal clear display
- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief
- Durably constructed cable, with high quality HD15 connectors

Hårdvara

Garantipolicy	Lifetime
Kontaktplätering	Nickel
Kabelmanteltyp	PVC - Polyvinyl Chloride
Kabelskärmning	Aluminiummylarfolie med flätning
Brandteknisk klass	CMG-klass (General Purpose)
Antal ferriter	1
Rättsliga godkännanden	UL2919

Prestanda

Impedans	75 Ohm
----------	--------

Kontakt(er)

Connector A	VGA (15-stifts, High Density D-Sub)
Connector B	VGA (15-stifts, High Density D-Sub)

Miljö

Drifttemperatur	0 to 60 °C
Förvaringstemperatur	-20 to 80 °C
Luftfuktighet	0 - 80 %RH

Utseende

Färg	Svart
Tråddimension	28 AWG
Maximal kontaktdimension	1.3 in [34 mm]
Kabellängd	39.4 in [100 cm]
Yttre kabelldiameter	0.4 in [9 mm]
Produktlängd	39.4 in [100.0 cm]



Produktbredd	0.2 in [5 mm]
Produkt höjd	0.2 in [5 mm]
Produktvikt	6.9 oz [195.0 g]

Förpackning

Förpackningsantal	1
Package Length	8.7 in [22.0 cm]
Package Width	7.9 in [20.0 cm]
Package Height	0.7 in [17.0 mm]
Fraktvikt (förpackning)	7.2 oz [204.0 g]

Vad det är i lådan

Ingår i paketet	1 m Coax High Resolution Monitor VGA Cable - HD15 M/M Nuts
-----------------	---

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

