

## 1m Coax High Resolution Monitor VGA Cable - HD15 M/M

**Product ID:** MXTMMHQ1M



The MXTMMHQ1M High Resolution VGA Cable (1-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

### **Certifications, Reports and Compatibility**

#### **Applications**

- Supports high resolution VGA monitors (1920x1200)
- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable

#### **Features**

- Triple coaxial + twisted-pair wire for crystal clear display
  - Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
  - High quality VGA connectors with molded PVC strain relief
  - Durably constructed cable, with high quality HD15 connectors
-

## Hardware

|                       |                                |
|-----------------------|--------------------------------|
| Warranty              | Lifetime                       |
| Connector Plating     | Nickel                         |
| Cable Jacket Material | PVC - Polyvinyl Chloride       |
| Cable Shield Material | Aluminum-Mylar Foil with Braid |
| Fire Rating           | CMG Rated (General Purpose)    |
| Number of Ferrites    | 1                              |
| Regulatory Approvals  | UL2919                         |

---

## Performance

|           |        |
|-----------|--------|
| Impedance | 75 Ohm |
|-----------|--------|

---

## Connector(s)

|             |                                  |
|-------------|----------------------------------|
| Connector A | VGA (15 pin, High Density D-Sub) |
| Connector B | VGA (15 pin, High Density D-Sub) |

---

## Environmental

|                       |             |
|-----------------------|-------------|
| Operating Temperature | 0 to 60 C   |
| Storage Temperature   | -20 to 80 C |
| Humidity              | 0 - 80 %RH  |

---

## Physical Characteristics

|                         |                    |
|-------------------------|--------------------|
| Color                   | Black              |
| Wire Gauge              | 28 AWG             |
| Max Connector Dimension | 1.3 in [34 mm]     |
| Cable Length            | 39.4 in [100 cm]   |
| Cable OD                | 0.4 in [9 mm]      |
| Product Length          | 39.4 in [100.0 cm] |
| Product Width           | 0.2 in [5 mm]      |
| Product Height          | 0.2 in [5 mm]      |



Weight of Product 6.9 oz [195.0 g]

---

**Packaging  
Information**

Package Quantity 1

Package Length 8.7 in [22.0 cm]

Package Width 7.9 in [20.0 cm]

Package Height 0.7 in [17.0 mm]

Shipping (Package)  
Weight 7.2 oz [204.0 g]

---

**What's in the  
Box**

Included in Package 1 m Coax High Resolution Monitor VGA Cable - HD15 M/M

Nuts

---

***\*Product appearance and specifications are subject to change without notice.***

