

2m Coax High Resolution Monitor VGA Video Cable - HD15 to HD15 M/M

Produkt ID: MXTMMHQ2M



The MXTMMHQ2M High Resolution VGA Cable (2-meter) is designed to provide the highest video quality possible through VGA, ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

Certifikat, rapporter och kompatibilitet

Användning

- Replace a worn-out or missing VGA monitor cable with this high quality, coax VGA cable
- Supports high resolution VGA monitors (1920x1200)

Funktioner

- Impedance matched at 75 Ohms for full brightness and vibrant picture color from your VGA monitor
- High quality VGA connectors with molded PVC strain relief
- Triple coaxial + twisted-pair wire for crystal clear display
- Durably constructed cable, with high quality HD15 connectors

Hrdvara	Garantipolicy	Lifetime
	Antal ledare	14
	Kontaktpltering	Nickel
	Kabelmanteltyp	PVC - Polyvinyl Chloride
	Kabelskrmning	Aluminiummylarfolie med fltning

	Brandteknisk klass	CMG-klass (General Purpose)
	Antal ferriter	1
Kontakt(er)	Connector A	VGA (15-stifts, High Density D-Sub)
	Connector B	VGA (15-stifts, High Density D-Sub)
Milj	Drifttemperatur	0 to 60 C
	Frvaringstemperatur	-20 to 80 C
	Luftfuktighet	0 - 80 %RH
Utseende	Frg	Svart
	Trddimension	28 AWG
	Kabellngd	6.6 ft [2 m]
	Produktlngd	6.6 ft [2 m]
	Produktbredd	1.2 in [30 mm]
	Produktljd	0.6 in [14 mm]
	Produktvikt	9.7 oz [275 g]
Frpackning	Frpackningsantal	1
	Package Length	8.7 in [2.2 cm]
	Package Width	7.9 in [2 cm]
	Package Height	2.0 in [52 mm]
	Fraktvikt (frpackning)	10.1 oz [285 g]
Vad det r i ldan	Ingr i paketet	2m Coax High Resolution Monitor VGA Cable - HD15 M/M

* *Produkters utseende och specifikationer kan komma att ndras utan frvarning.*

