

7m Coax High Resolution Monitor VGA Video Cable - HD15 to HD15 M/M

Product ID: MXTMMHQ7M



The MXTMMHQ7M 7m long VGA cable allows you to connect your VGA monitor or projector at distances of up to 25 feet from your computer, video switch or other VGA device. The high-resolution cable is designed to provide the highest video quality possible through VGA and is ideally suited for high resolution applications of 1920x1200 and above.

This durably constructed coaxial VGA video cable (HD15 to HD15) eliminates the picture "ghosting" and fuzzy images that are inherent to non-coaxial VGA cables, while delivering superior EMI interference protection by using ferrite cores near the connector ends.

This 7m VGA cable is backed by StarTech.com's lifetime warranty.

Certifications, Reports and Compatibility



Applications

- Connect a high-resolution display to a desktop PC or video switch, up to 7 meters away

Features

- 2x VGA HD15 male connectors
- Triple coaxial + twisted-pair wire for crystal clear display

- Impedance matched at 75 Ohms for full brightness and vibrant picture color
- Supports high resolution VGA monitors (1920x1200)

Hardware

Warranty	Lifetime
Number of Conductors	14
Connector Plating	Nickel
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Shield Material	Aluminum-Mylar Foil with Braid
Fire Rating	CMG Rated (General Purpose)

Connector(s)

Connector A	1 - VGA (15 pin, High Density D-Sub)
Connector B	1 - VGA (15 pin, High Density D-Sub)

Physical Characteristics

Color	Black
Wire Gauge	28 AWG
Cable Length	23.0 ft [7 m]
Product Length	23.0 ft [7.0 m]
Product Width	1.3 in [3.3 cm]
Product Height	0.6 in [1.6 cm]
Weight of Product	1.6 lb [0.7 kg]

Packaging Information

Package Quantity	1
Package Length	13.0 in [33.0 cm]
Package Width	9.9 in [25.2 cm]
Package Height	0.0 in [0.1 mm]

Shipping (Package) Weight	1.6 lb [0.7 kg]
------------------------------	-----------------

What's in the Box

Included in Package	1 - 7m Coax High Resolution Monitor VGA Cable - HD15 M/M
---------------------	--

****Product appearance and specifications are subject to change without notice.***