50cm Blue Slim CAT6 Cable, 10 Pack, Snagless, 100W PoE, UTP, LSZH, 28AWG Pure Bare Copper Wire, Slim RJ45 Network Patch Cord w/Strain Reliefs, Individually Tested

Product ID: N6PAT50CMBLS10PK



This slim CAT6 cable meets all Category 6 patch cable specifications to deliver a reliable Gigabit and Power over Ethernet (PoE) network connection in high-density network installations.

The Slim Cat6 Patch Cord is 36% thinner than standard Cat6 Ethernet cables, enabling greater airflow and heat dissipation in confined spaces. The Slim Cat6 Ethernet cable is also more flexible, for easier cable routing in crowded network racks and patch panels.

This cable features snagless connectors that protect the RJ45 clips during installation, reducing snags or breakage when routing through narrow gaps or in between devices.

The Slim Cat6 Cable features 50-microinch gold RJ45 contacts that ensure a precise fit to minimize wear and signal loss. The 4-pair Unshielded Twisted Pair (UTP) construction utilizes 28AWG Pure Bare Copper Wire for improved conductivity and low resistance. The flexible Low Smoke Zero Halogen (LSZH) flame-retardant jacket emits low smoke and toxic fumes when exposed to extreme heat or in the event of a fire. This enables safer installations in poorly-ventilated areas including some industrial settings, self-contained environments such as trains and aircraft, as well as residential settings where compliance with building codes must be considered.

Each cable is individually tested using a Fluke DSX2-8000 CableAnalyzer to meet ANSI/TIA-568.2-D Category 6 specifications, ensuring consistent signal integrity with minimal Near-End Crosstalk (NEXT) and Retun Loss (RL). Reliably deliver up to 100W of PoE++ to power a remote networking devices, including PoE switches and boardroom cameras. This Slim Cat6 Patch Cable complies with IEEE 802.3bt Type 4 PoE++ specifications.

Certifications, Reports and Compatibility

Applications

• Route slim Cat6 cables to enable greater airflow and heat dissipation in confined spaces.Flexible Low Smoke Zero Halogen (LSZH) jacket is ideal for routing in crowded rackmount setups and patch panels.

• Standardize structured cabling deployments with a broad selection of cable lengths, colors, and pack configurations designed for scalable installations and multi-site rollouts

• Connect out-of-band management hardware, console ports, wireless access points, and network infrastructure devices with full Cat6 performance for everyday IT operations

Features

• Practical 10 Pack: Deploy faster and more organized with a 10-pack of Slim Cat6 patch cables, ideal for large-scale installations; Slim Cat6 Cables are 36% thinner than standard Cat6 for easier routing in dense IT setups

• Built for Performance: Supports 10Gbps speeds and 100W PoE++ (IEEE 802.3bt Type 4) with 28AWG pure bare copper wire and 50-microinch gold-plated contacts for reliable signal integrity; Flexible Low-Smoke Zero Halogen (LSZH) jacket withstands tight bends

• Tested for Reliable Uptime: Compliant with ANSI/TIA-568-C.2 standards for guaranteed Cat6 performance up to 250MHz; Individually Tested for minimal Near-End Crosstalk (NEXT) and Return Loss (RL)

• Enhance Access and Airflow: Slim Cat6 cables improve access for troubleshooting and airflow between devices; Connect reliably to PoE devices such as IP or boardroom cameras; LSZH jacket is safe for confined spaces and emits low-toxicity fumes if combusted

• The IT Pro's Choice: Designed for reliability in edge and on-prem deployments, our network cables are lab-tested and field-proven for seamless integration and maximum uptime; Backed by free lifetime 24/5 multi-lingual technical assistance

General		
	UPC	065030924078
	Package Quantity	10
	Warranty	Lifetime
Power		
	Power Delivery	100W
Physical & Environmental		
	Color	Blue
	Wire Gauge	28 AWG

	Conductor Type	Stranded Copper
	Cable Length	19.7 in [50 cm]
	Cable OD	0.1 in [3.6 mm]
	Product Length	19.7 in [50 cm]
	Product Width	0.5 in [11.6 mm]
	Product Height	0.5 in [13.7 mm]
	Weight of Product	0.6 oz [16 g]
	Operating Temperature	10C ~ 60C (50F to 140F)
	Storage Temperature	-20C ~ 60C (-4F to 140F)
	Humidity	10% ~ 80%
Performance		
	Maximum Data Transfer Rate	10 Gbps
	Cable Rating	CAT6 - 250 MHz
Hardware		
	Number of Conductors	4 Pair UTP
	Connector Plating	Gold
	Cable Jacket Material	LSZH (Low Smoke Zero Halogen)
	Cable Type	Snagless
	Wiring Standard	TIA/EIA-568-B.1-2001 T568B
Packaging & In-the-Box		
	Included in Package	1 - Slim Cat6 patch cable
	Package Width	9.4 in [24 cm]
	Package Depth	8.7 in [22 cm]
	Package Height	0.6 in [15 mm]
	Shipping (Package) Weight	9.9 oz [281 g]

Connector(s)		
	Connector 1 (Quantity)	1
	Connector 1	RJ-45
	Connector 2 (Quantity)	1
	Connector 2	RJ-45

Product appearance and specifications are subject to change without notice.