

10ft CAT6 Ethernet Cable - Blue CAT 6 Gigabit Ethernet Wire -250MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Individually Tested

ID del Producto: N6PATCH10BL



The N6PATCH10BL Cat 6 Patch Cable (10 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable blue PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Diseñado para utilizar con redes Gigabit
- Conecta un hub a un panel de distribución
- Conecta una estación de trabajo a una placa de pared

Características

- Alambre de cobre alta calidad con 24AWG
- Certificación ETL
- Protectores de clip RJ45
- Cuidadosamente fabricado y probado, para mantener los niveles de diafonía (Near End Crosstalk) en límites aceptables
- Cubiertas de colores para ayudar a codificarlo por color de sección o departamento
- Alivio de tensión moldeado que previene que el cable se doble en ángulos agudos por el conector RJ45, con el fin de minimizar la tensión al punto de terminación del conector
- Fabricado con componentes de la más alta calidad

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 pair UTP
Cable Tipo Jacket	PVC - Polyvinyl Chloride
Grado de Inflamabilidad	Clasificación CMG (uso general)
Estándar de Cableado	TIA/EIA-568-B.1-2001 T568B

Rendimiento

Clasificación de Cables CAT6 - 250 MHz

Conector(es)

Conector A	1 - RJ-45
Conector B	1 - RJ-45

Requisitos Ambientales

Temperatura Operativa	-20°C to 80°C (-4°F to 176°F)
Temperatura de Almacenamiento	-20°C to 80°C (-4°F to 176°F)
Humedad	15 ~ 65%

Características Físicas

Color	Azul
Calibre del Conductor	24 AWG
Tipo de conductor	Cobre trenzado
Longitud del Cable	10.0 ft [3.0 m]
Longitud del Producto	10.0 ft [3.0 m]
Peso del Producto	4.7 oz [132.7 g]

Información de la Caja

Cantidad de Paquetes	1
Longitud de la Caja	6.6 in [16.8 cm]
Ancho de la Caja	7.8 in [19.8 cm]
Altura de la Caja	0.9 in [2.4 cm]
Peso (de la Caja) del Envío	6.1 oz [172.0 g]

Información Acerca de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.