

10ft CAT6 Cable - Gray CAT6 Ethernet Cable - Gigabit Ethernet Wire - 250MHz 100W PoE RJ45 UTP CAT 6 Network/Patch Cord Snagless - Individually Tested

ID del Producto: N6PATCH10GR



The N6PATCH10GR Cat 6 Patch Cable (10 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable gray PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Características

- **CABLE ETHERNET CAT6 DE ALTO RENDIMIENTO:** 100% de cobre para conexiones de 1 a 5Gbps sin errores. 10Gbps a hasta 48,7m. Sometido a pruebas Fluke, y cumple con las normas ETL y ANSI/TIA-568-2.D de CAT6
- **POE SUPPORT:** CAT6 cable with 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- **QUALITY CONSTRUCTION:** UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- **EASY INSTALLATION:** 10 foot snagless network cable for easy installation & flexible disconnection in wiring conduits; CAT6 patch cable/cord is compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- **SPECS:** Length: 10ft (3m) | Color: Gray CAT 6 Cable | 250 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/TIA-568-B| Warranty: Lifetime

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 pair UTP
Cable Tipo Jacket	PVC - Polyvinyl Chloride
Grado de Inflamabilidad	Clasificación CMG (uso general)

Estándar de Cableado TIA/EIA-568-B.1-2001 T568B

Rendimiento

Clasificación de Cables CAT6 - 250 MHz

Conector(es)

Conector A 1 - RJ-45

Conector B 1 - RJ-45

Requisitos Ambientales

Temperatura Operativa -20°C to 80°C (-4°F to 176°F)

Temperatura de Almacenamiento -20°C to 80°C (-4°F to 176°F)

Humedad 15 ~ 65%

Características Físicas

Color Gris

Calibre del Conductor 24 AWG

Tipo de conductor Cobre trenzado

Longitud del Cable 10.0 ft [3.0 m]

Longitud del Producto 10.0 ft [3.0 m]

Peso del Producto 5.3 oz [151 g]

Información de la Caja

Cantidad de Paquetes 1

Longitud de la Caja 8.7 in [22 cm]

Ancho de la Caja 7.9 in [20 cm]

Altura de la Caja 0.7 in [19 mm]

Peso (de la Caja) del Envío 5.3 oz [150 g]

Contenido de la
Caja

Incluido en la Caja

1 - 10 ft Gray Snagless Cat6 UTP Patch Cable - ETL
Verified

Información Acerca
de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.