

10ft CAT6 Cable - Red CAT6 Ethernet Cable - Gigabit Ethernet Wire - 250MHz 100W PoE RJ45 UTP CAT 6 Network/Patch Cord Snagless - Individually Tested

ID del Producto: N6PATCH10RD



The N6PATCH10RD Cat 6 Patch Cable (10 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable red PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Diseñado para usarse con redes Fast Ethernet
- Permite realizar conexiones desde el concentrador al panel de distribución
- Permite conectar la estación de trabajo a un tomacorriente de pared

Características

- CABLE ETHERNET CAT6 DE ALTO RENDIMIENTO: 100% de cobre para conexiones de 1 a 5Gbps sin errores. 10Gbps a hasta 48,7m. Sometido a pruebas Fluke, y cumple con las normas ETL y ANSI/TIA-568-2.D de CAT6
- Cuidadosamente fabricado y probado para mantener el Near End Crosstalk (NEXT) dentro de los límites aceptables
- Fabricado con componentes de máxima calidad
- Alambre de cobre calibre 0,25mm² de alta calidad
- Certificación ETL

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 pair UTP
Cable Tipo Jacket	PVC - Polyvinyl Chloride
Grado de Inflamabilidad	Clasificación CMG (uso general)
Estándar de Cableado	TIA/EIA-568-B.1-2001 T568B

Rendimiento

Clasificación de Cables	CAT6 - 250 MHz
-------------------------	----------------

Conector(es)		
	Conector A	1 - RJ-45
	Conector B	1 - RJ-45
Requisitos Ambientales		
	Temperatura Operativa	-20°C to 80°C (-4°F to 176°F)
	Temperatura de Almacenamiento	-20°C to 80°C (-4°F to 176°F)
	Humedad	15 ~ 65%
Características Físicas		
	Color	Rojo
	Calibre del Conductor	24 AWG
	Tipo de conductor	Cobre trenzado
	Longitud del Cable	10.0 ft [3.0 m]
	Longitud del Producto	10.0 ft [3.0 m]
	Peso del Producto	4.7 oz [132 g]
Información de la Caja		
	Cantidad de Paquetes	1
	Longitud de la Caja	6.9 in [17.6 cm]
	Ancho de la Caja	7.9 in [20 cm]
	Altura de la Caja	0.9 in [2.3 cm]
	Peso (de la Caja) del Envío	5.1 oz [144.0 g]
Contenido de la Caja		
	Incluido en la Caja	1 - 10 ft Red Snagless Cat6 UTP Patch Cable - ETL Verified

Información Acerca
de la Garantía

Warranty

De Por Vida

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.