

Câble réseau Cat6 Gigabit UTP sans crochet de 3m - Cordon Ethernet RJ45 anti-accroc - M/M - Blanc

N° de produit: N6PATCH10WH



The N6PATCH10WH Cat 6 Patch Cable (10 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable white PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certifications, rapports et compatibilité



Applications

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Spécifications techniques

- High quality 24 AWG copper wire
- ANSI/TIA-568-2.D Category 6 Compliance
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Individually Tested to comply w/ANSI/TIA-568-2.D Category 6
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 10 foot snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 10ft (3m) | Color: White | 250 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | Warranty: Lifetime

Matériel

Politique de garantie	Lifetime
Nombre de conducteurs	4 pair UTP
Type de gaine de câble	PVC - Polyvinyl Chloride

	Résistance au feu	Homologué CMG (usage général)
	Norme de câblage	TIA/EIA-568-B.1-2001 T568B
Performance		
	Calibre du câble	CAT6 - 250 MHz
Connecteur(s)		
	Connecteur A	1 - RJ-45
	Connecteur B	1 - RJ-45
Conditions environnementales		
	Température de fonctionnement	-20°C to 80°C (-4°F to 176°F)
	Température de stockage	-20°C to 80°C (-4°F to 176°F)
	Humidité	15 ~ 65%
Caractéristiques physiques		
	Couleur	Blanc
	Calibre du fil	24 AWG
	Type de conducteur	Cuivre torsadé
	Longueur de câble	10.0 ft [3.0 m]
	Longueur du produit	10.0 ft [3.0 m]
	Poids du produit	5.0 oz [142 g]
Informations d'emballage		
	Quantité par paquet	1
	Longueur du Paquet	6.8 in [17.3 cm]
	Largeur du Colis	7.8 in [19.7 cm]
	Hauteur du Paquet	1.0 in [2.6 cm]

Poids brut	5.2 oz [148.0 g]
------------	------------------

Contenu du paquet

Inclus dans le paquet	1 - 10 ft White Snagless Cat6 UTP Patch Cable - ETL Verified
-----------------------	--

Informations de garantie

Warranty	À Vie
----------	-------

* L'apparence et les spécifications du produit peuvent être modifiées sans préavis