

3 ft. CAT6 Ethernet cable - 10 Pack - Blue CAT6 Patch Cord - Snagless RJ45 Connectors - 24 AWG Copper Wire – UTP Ethernet Cable

Produkt-ID: N6PATCH3BL10PK



This CAT6 Ethernet cable bulk pack meets all Category 6 cable specifications, to deliver a reliable Gigabit network connection.

These CAT6 patch cables are built using 100% copper wire and are tested to comply with ANSI/TIA 568 C.2 Category 6 requirements. We don't use copper-clad aluminum (CCA) wire, which is subject to problems like weak power delivery, heat buildup, equipment damage and possibly fire.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

Each CAT6 cable is manufactured using high-quality copper conductors and carefully constructed and tested to keep Near-End Crosstalk (NEXT) well within acceptable limits. The patch cables are constructed with 24 AWG copper wire, to ensure peak performance for demanding Ethernet applications such as Power-over-Ethernet and 4K or 1080p video streaming.

For trouble-free cable runs, these durable cables feature snagless connectors that protect the RJ45 clips during installation, making them less likely to snag or break.

N6PATCH3BL10PK is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **100% COPPER WIRING:** Each CAT6 Ethernet cable is built with 100% copper wiring to prevent weak power delivery and equipment damage, compared to copper-clad aluminum wire cables
- **ANSI/TIA-568-D CATEGORY 6 COMPLIANCE:** Each CAT6 patch cord in this 10 pack is tested to comply with ANSI/TIA-568-D Category 6 requirements ensuring high-speed data transmission with reduced crosstalk and enhanced signal integrity
- **CABLE PERFORMANCE:** Length: 3 ft. (1 m) Color: Blue | Cable Structure: 4 Pair UTP | Connector Type: Snagless | Jacket Material: PVC | Wire Gauge: 24 AWG | Wiring Standard: ANSI/T568B
- **EASY INSTALLATION:** Blue snagless Ethernet cords won't get caught in wiring conduits during installation; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- **CAT6 PATCH CABLE MULTIPACK:** This 10 pack of 3 ft. Blue patch cords is a convenient and affordable option for businesses in need of multiple snagless ethernet cables

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	4 pair UTP
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandsklasse	Ausgelegt gemäß CMG (Mehrzweck)
Kabeltyp	Nahtlos geformt
Verkabelungsstandard	TIA/EIA-568-B.1-2001 T568B

Leistung

Kabelnennwerte	CAT6 - 250 MHz
----------------	----------------

Steckverbinder

Steckverbinder A	1 - RJ-45
Steckverbinder B	1 - RJ-45

Umgebungsbeding

ungen

Betriebstemperatur	-20°C to 80°C (-4°F to 176°F)
Lagertemperatur	-20°C to 80°C (-4°F to 176°F)
Feuchtigkeit	15 ~ 65%

Physische Eigenschaften

Farbe	Blau
Drahtstärke	24 AWG
Leitungstyp	Feindrähtiges Kupfer
Kabellänge	3.0 ft [0.9 m]
Produktlänge	36.0 in [91.5 cm]
Produktbreite	0.5 in [1.2 cm]
Produkthöhe	0.6 in [1.5 cm]
Produktgewicht	1.6 oz [46 g]

Verpackungsinform ationen

Paketmenge	10
Paketlänge	8.4 in [21.4 cm]
Paketbreite	8.6 in [21.9 cm]
Pakethöhe	2.4 in [6.2 cm]
Versandgewicht (Verpackung)	1.0 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten	10 - CAT6-Kabel, 91 cm
--------------------	------------------------

Garantieinformatio nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.