

3ft CAT6 Ethernet Cable - Green CAT 6 Gigabit Ethernet Wire -250MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Individually Tested

ID prodotto: N6PATCH3GN



The N6PATCH3GN Cat 6 Patch Cable (3 ft) meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections, and features a durable green PVC jacket that enables you to color code your network cable runs as needed.

To ensure long-lasting performance, this high quality Cat 6 patch cable features a snagless design that protects the RJ45 connector clips from damage and makes the cable less prone to snagging during installation. The cable also features molded PVC strain relief that prevents the RJ45 connector termination points from bending at sharp angles - reducing the risk of cable damage, which could decrease network performance.

Constructed of only top quality materials, this Cat 6 Patch Cord delivers reliable performance and is backed by our Lifetime Warranty.

StarTech.com Cat6 cables are manufactured using high-quality copper conductors. While many cable manufacturers offer a "cheaper" cable based on a copper-coated aluminum core, we make no compromises on quality to ensure you receive top value and performance for your network cable investment.

This Cat6 cable is constructed with 24 gauge copper wire, to support a broad range of Ethernet applications such as Power over Ethernet (PoE). Because we use a high quality copper wire, our cables easily sustain the power required for Power over Ethernet applications, whereas the inferior quality offered by copper-coated aluminum cables may be subject to insufficient power delivery, heat buildup, equipment damage and potentially, fire.

This Cat 6 patch cable offers high quality connectors comprised of 50-micron gold, to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

Certificazioni, report e compatibilità



Applicazioni

- Progettato per l'utilizzo con reti Gigabit
- Consente il collegamento dall'hub al pannello di distribuzione
- Consente il collegamento della workstation alla presa a muro

Caratteristiche

- Cappucci colorati per codifica dei colori a sezioni
- Il pressacavo modellato impedisce che il cavo si pieghi in corrispondenza di angoli acuti sul connettore RJ45, riducendo al minimo la tensione nel punto terminale della presa
- CAVO ETHERNET CAT6 AD ALTE PRESTAZIONI: cavo in rame 100% per connessioni Multi Gigabit a più velocità da 1/2,5/5 Gbps senza errori; 10 Gbps fino a 55 m; conforme ai requisiti ANSI/TIA-568-2.D Cat 6 -Testato individualmente
- SUPPORTO POE: i conduttori in rame intrecciato da 0,20mm² e il cablaggio UL supportano fino a 100 W per i dispositivi PoE come sistemi di sicurezza e telefoni VOIP. La conformità con IEEE 802.3bt e alimentazione DTE impedisce il surriscaldamento dei cavi
- COSTRUZIONE DI QUALITÀ: filo certificato ETL & UL; i connettori placcati in oro da 50 micron prevengono la ruggine/corrosione riducendo costose riparazioni alla rete; il rivestimento in PVC di alta qualità resiste ai danni da piegatura o sfilacciamento
- EASY INSTALLATION: 3 foot snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 3ft (1m) | Color: Green | 250 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | Warranty: Lifetime

Hardware

Norme di garanzia	Lifetime
Numero di conduttori	4 Pair UTP

	Tipo guaina cavo	PVC - Polyvinyl Chloride
	Classe di resistenza al fuoco	Classe CMG (uso generale)
	Standard cablaggio	TIA/EIA-568-B.1-2001 T568B
Prestazioni	Classe cavo	CAT6 - 250 MHz
Connettore/i	Connettore A	1 - RJ-45
	Connettore B	1 - RJ-45
Ambientale	Temperatura d'esercizio	-20°C to 80°C (-4°F to 176°F)
	Temperatura di conservazione	-20°C to 80°C (-4°F to 176°F)
	Umidità	15 ~ 65% RH
Caratteristiche fisiche	Colore	Verde
	Diametro filo	24 AWG
	Tipo di conduttore	Rame intrecciato
	Lunghezza del cavo	3.0 ft [0.9 m]
	Lunghezza prodotto	3.0 ft [0.9 m]
	Larghezza prodotto	0.0 in [0.0 mm]
	Altezza prodotto	0.0 in [0.0 mm]
	Peso prodotto	2.0 oz [56.0 g]
Informazioni confezione	Quantità confezione	1

Lunghezza Confezione	7.1 in [18.0 cm]
Larghezza del Pacco	7.8 in [19.9 cm]
Altezza del Pacco	0.8 in [2.1 cm]
Peso spedizione (confezione)	2.0 oz [58.0 g]

Contenuto della
confezione

Incluso nella confezione	1 - 3 ft Green Snagless Cat6 UTP Patch Cable - ETL Verified
-----------------------------	--

Informazioni sulla
garanzia

Warranty	A vita
----------	--------

* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.