

5ft CAT6 Ethernet Cable - Black CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Fluke Tested/Wiring is UL Certified/TIA

ID prodotto: N6PATCH5BK



This 5-foot Cat6 cable meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections. Plus, the cable features a durable black PVC jacket that enables you to color code your network cable runs as needed.

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features molded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

Get the highest value for your cable investment with our Cat 6 cables, each one manufactured using high-quality copper conductors.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The N6PATCH5BK is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certificazioni, report e compatibilità

## Applicazioni

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

## Caratteristiche

- High quality 24 AWG copper wire
- ETL Verified
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Fluke patch cord tested to comply w/ANSI/TIA-568-2.D Category 6; ETL Verified
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: ETL & UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 5 foot snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 5ft (1.5m) | Color: Black | 650 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | ETL Verified | Warranty: Lifetime

---

### Hardware

Norme di garanzia	Lifetime
Numero di conduttori	4 Pair UTP
Placcatura connettori	Oro
Tipo guaina cavo	PVC - Polyvinyl Chloride
Classe di resistenza al fuoco	Classe CMG (uso generale)
Tipo cavo	Antigroviglio

	Standard cablaggio	TIA/EIA-568-B.1-2001 T568B
<hr/>		
Prestazioni	Classe cavo	CAT6 - 650 MHz
<hr/>		
Connettore/i	Connettore A	RJ-45
	Connettore B	RJ-45
<hr/>		
Caratteristiche fisiche	Colore	Nero
	Diametro filo	24 AWG
	Tipo di conduttore	Rame intrecciato
	Lunghezza cavo	5.0 ft [1.5 m]
	Lunghezza prodotto	5.0 ft [1.5 m]
	Larghezza prodotto	0.5 in [11.5 mm]
	Altezza prodotto	0.6 in [15 mm]
	Peso prodotto	2.4 oz [68 g]
<hr/>		
Informazioni confezione	Quantità confezione	1
	Package Length	8.7 in [22 cm]
	Package Width	7.9 in [20 cm]
	Package Height	0.5 in [12 mm]
	Peso spedizione (confezione)	2.7 oz [77 g]
<hr/>		
Contenuto della confezione	Incluso nella confezione	5 ft. Cat6 Patch Cable - Black



---

\* L'aspetto e le specifiche dell'articolo sono soggetti a modifiche senza preavviso.

