

5 ft. CAT6 Ethernet cable - 10 Pack - Blue CAT6 Patch Cord - Snagless RJ45 Connectors - 24 AWG Copper Wire – UTP Ethernet Cable

Produkt-ID: N6PATCH5BL10PK



This CAT6 Ethernet cable bulk pack meets all Category 6 cable specifications, to deliver a reliable Gigabit network connection.

Protect Your Equipment

These CAT6 patch cables are built using 100% copper wire and are tested to comply with ANSI/TIA 568 C.2 Category 6 requirements. We don't use copper-clad aluminum (CCA) wire, which is subject to problems like weak power delivery, heat buildup, equipment damage and possibly fire.

The 50-micron gold connectors deliver optimum conductivity and eliminate signal loss due to oxidation or corrosion.

High-Quality Construction

Each CAT6 cable is manufactured using high-quality copper conductors and carefully constructed and tested to keep Near-End Crosstalk (NEXT) well within acceptable limits. The patch cables are constructed with 24 AWG copper wire, to ensure peak performance for demanding Ethernet applications such as Power-over-Ethernet and 4K or 1080p video streaming.

Easily Install Your Network Cables

For trouble-free cable runs, these durable cables feature snagless connectors that protect the RJ45 clips during installation, making them less likely to snag or break.

The CAT6 Ethernet cables also feature molded boots which offer strain relief by stopping the RJ45 connectors from bending at sharp angles. This reduces the risk of cable damage, which could decrease network connectivity and performance.

N6PATCH5BL10PK is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **100% COPPER WIRING:** Each CAT6 Ethernet cable is built with 100% copper wiring to prevent weak power delivery and equipment damage, compared to copper-clad aluminum wire cables
- **ANSI/TIA-568-D CATEGORY 6 COMPLIANCE:** Each CAT6 patch cord in this 10 pack is tested to comply with ANSI/TIA-568-D Category 6 requirements ensuring high-speed data transmission with reduced crosstalk and enhanced signal integrity
- **CABLE PERFORMANCE:** Length: 5 ft. (1.5 m) Color: Blue | Cable Structure: 4 Pair UTP | Connector Type: Snagless | Jacket Material: PVC | Wire Gauge: 24 AWG | Wiring Standard: ANSI/T568B
- **EASY INSTALLATION:** Blue snagless Ethernet cords won't get caught in wiring conduits during installation; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- **CAT6 PATCH CABLE MULTIPACK:** This 10 pack of 5 ft. Blue patch cords is a convenient and affordable option for businesses in need of multiple snagless ethernet cables

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	4 pair UTP
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Feuerwiderstandssklasse	Ausgelegt gemäß CMG (Mehrzweck) e
Kabeltyp	Nahtlost geformt
Verkabelungsstandard	TIA/EIA-568-B.1-2001 T568B

Leistung

Kabelnennwerte		CAT6 - 250 MHz
Steckverbinder	Steckverbinder A	1 - RJ-45
	Steckverbinder B	1 - RJ-45
Umgebungsbedingungen		
	Betriebstemperatur	-20°C to 80°C (-4°F to 176°F)
	Lagertemperatur	-20°C to 80°C (-4°F to 176°F)
	Feuchtigkeit	15 ~ 65%
Physische Eigenschaften		
	Farbe	Blau
	Drahtstärke	24 AWG
	Leitungstyp	Feindrähtiges Kupfer
	Kabellänge	5.0 ft [1.5 m]
	Produktlänge	60.0 in [152.5 cm]
	Produktbreite	0.5 in [1.2 cm]
	Produkthöhe	0.6 in [1.5 cm]
	Produktgewicht	3.9 oz [110 g]
Verpackungsinformationen		
	Paketmenge	10
	Paketlänge	8.2 in [20.9 cm]
	Paketbreite	8.5 in [21.7 cm]
	Pakethöhe	3.9 in [9.9 cm]
	Versandgewicht (Verpackung)	1.6 lb [0.7 kg]

Verpackungsinhalt

Im Paket enthalten	10 - CAT6-Kabel, 1,5 m
--------------------	------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.