

## 5ft CAT6 Ethernet Cable - White CAT 6 Gigabit Ethernet Wire -250MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Individually Tested

Produkt-ID: N6PATCH5WH



This Cat6 cable delivers reliable Gigabit network connections, which ensures high-performance capability for your demanding Ethernet applications.

This 5-foot white patch cable is perfect for standard applications such as connecting from a wall jack to your laptop docking station or desktop computer.

For easier network installations, our Cat6 patch cables are available in a wide variety of lengths and colors. This ensures you have the right size of cable available when you need it and it lets you color code your connections for a more organized setup.

For trouble-free cable runs, this durable cable features snagless connectors that protect the RJ45 clips during installation, making them less likely to snag or break.

The cable also features molded boots which offer connector strain relief by stopping the RJ45 connector termination points from bending at sharp angles. This reduces the risk of damage to the cable, which could decrease network connectivity and performance.

Get the highest value for your cable investment with our Cat6 Ethernet cables. Each of our patch cables is manufactured using high-quality copper conductors and they are carefully constructed and tested, to keep Near-End Crosstalk (NEXT) well within acceptable limits.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet and 4K or 1080p video streaming, using cables that include 24 AWG copper.

You can rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The N6PATCH5WH is backed by StarTech.com's lifetime warranty for guaranteed reliability.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

## Merkmale

- High-quality 24 AWG copper wire
- ANSI/TIA-568-2.D Category 6 Compliance
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Individually Tested to comply w/ANSI/TIA-568-2.D Category 6
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 5 foot snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 5ft (1.5m) | Color: White | 250 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B| Warranty: Lifetime

---

### Hardware

Garantiebestimmungen Lifetime

Anzahl von Leitern 4 pair UTP

|                          |                                 |
|--------------------------|---------------------------------|
| Steckverbinderplatten    | Gold                            |
| Typ der Kabelummantelung | PVC - Polyvinyl Chloride        |
| Feuerwiderstandssklasse  | Ausgelegt gemäß CMG (Mehrzweck) |
| Verkabelungsstandard     | TIA/EIA-568-B.1-2001 T568B      |
| <hr/>                    |                                 |
| Leistung                 |                                 |
| Kabelnennwerte           | CAT6 - 250 MHz                  |
| <hr/>                    |                                 |
| Steckverbinder           |                                 |
| Steckverbinder A         | 1 - RJ-45                       |
| Steckverbinder B         | 1 - RJ-45                       |
| <hr/>                    |                                 |
| Umgebungsbedingungen     |                                 |
| Betriebstemperatur       | -20°C to 80°C (-4°F to 176°F)   |
| Lagertemperatur          | -20°C to 80°C (-4°F to 176°F)   |
| Feuchtigkeit             | 15 ~ 65%                        |
| <hr/>                    |                                 |
| Physische Eigenschaften  |                                 |
| Farbe                    | Weiß                            |
| Drahtstärke              | 24 AWG                          |
| Leitungstyp              | Feindrähtiges Kupfer            |
| Kabellänge               | 5.0 ft [1.5 m]                  |
| Produktlänge             | 5.0 ft [1.5 m]                  |
| Produktgewicht           | 2.5 oz [70 g]                   |
| <hr/>                    |                                 |
| Verpackungsinformationen |                                 |
| Paketmenge               | 1                               |
| Paketlänge               | 5.8 in [14.7 cm]                |

|                                |                  |
|--------------------------------|------------------|
| Paketbreite                    | 6.3 in [16.0 cm] |
| Pakethöhe                      | 1.5 in [3.9 cm]  |
| Versandgewicht<br>(Verpackung) | 2.9 oz [82.0 g]  |

---

#### Verpackungsinhalt

|                    |                      |
|--------------------|----------------------|
| Im Paket enthalten | 1 - Cat6 patch cable |
|--------------------|----------------------|

---

#### Garantieinformationen

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.