

75ft CAT6 Ethernet Cable - Black CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Fluke Tested/Wiring is UL Certified/TIA

Produkt ID: N6PATCH75BK



This 75-foot Cat6 cable meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections. Plus, the cable features a durable black PVC jacket that enables you to color code your network cable runs as needed.

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features molded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

Get the highest value for your cable investment with our Cat 6 cables, each one manufactured using high-quality copper conductors.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The N6PATCH75BK is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifikat, rapporter och kompatibilitet



Användning

- Framtagen för att användas med gigabit-nätverk
- Kopplar från hubb till distributionspanel
- Anslut en arbetsstation till ett vägguttag
- Förläng ditt Gigabit-nätverks täckning med 22,8 m

Funktioner

- Färgade huvor så att man kan färgkoda olika avdelningar
- Gjuten dragavlastning hindrar att kabeln böjs i skarpa vinklar vid RJ45-kontakten, vilket i sin tur minskar påfrestningarna på kontaktens spets
- Tillverkad av komponenter med toppkvalitet
- Högkvalitativ 0,25 mm² koppartråd
- ETL-godkänd
- Skydd till RJ45-kontakter
- Tillverkad och testad med omsorg för att bakåtoverhörning (NEXT) ska ligga väl inom godkända gränser

Hårdvara

Garantipolicy	Lifetime
Antal ledare	4 Pair UTP
Kabelmanteltyp	PVC - Polyvinyl Chloride
Brandteknisk klass	CMG-klass (General Purpose)
Kabeltyp	Hakfri
Kabelstandard	TIA/EIA-568-B.1-2001 T568B

Prestanda

Kabelklassificering CAT6 - 650 MHz

Kontakt(er)

Connector A 1 - RJ-45

Connector B 1 - RJ-45

Miljö

Drifttemperatur -20°C to 80°C (-4°F to 176°F)

Förvaringstemperatur -20°C to 80°C (-4°F to 176°F)

Luftfuktighet 15-65 %

Utseende

Färg Svart

Tråddimension 24 AWG

Ledningstyp Tvinnad koppar

Kabellängd 75.0 ft [22.9 m]

Produktlängd 75.0 ft [22.9 m]

Produktbredd 0.5 in [1.3 cm]

Produkthöjd 0.6 in [1.6 cm]

Produktvikt 2.3 lb [1.0 kg]

Förpackning

Förpackningsantal 1

Paketets längd 10.4 in [26.3 cm]

Paketets bredd 9.9 in [25.1 cm]

Paketets höjd 1.9 in [4.8 cm]

Fraktvikt (förpackning) 2.1 lb [1.0 kg]

Vad det är i lådan

Ingår i paketet 1 - 75 ft. Cat6 Patch Cable - Black

Warranty
Information

Warranty

Livslängd

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.