

75ft CAT6 Ethernet Cable - Red CAT 6 Gigabit Ethernet Wire -650MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Fluke Tested/Wiring is UL Certified/TIA

Nº de produit: N6PATCH75RD



This 75-foot Cat6 cable meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections. Plus, the cable features a durable red PVC jacket that enables you to color code your network cable runs as needed.

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features molded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

Get the highest value for your cable investment with our Cat 6 cables, each one manufactured using high-quality copper conductors.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The N6PATCH75RD is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certifications, rapports et compatibilité



Applications

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet
- Extend the reach of your Gigabit network devices by 75 ft

Spécifications techniques

- High quality 24 AWG copper wire
- ANSI/TIA-568-2.D Category 6 Compliance
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Fluke patch cord tested to comply w/ANSI/TIA-568-2.D Category 6
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 75 foot snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 75ft (22.8m) | Color: Red | 650 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | Warranty: Lifetime

Matériel

Politique de garantie Lifetime

Nombre de conducteurs 4 Pair UTP

Type de gaine de câble PVC - Polyvinyl Chloride

	Résistance au feu	Homologué CMG (usage général)
	Type de câble	Sans crochet
	Norme de câblage	TIA/EIA-568-B.1-2001 T568B
Performance		
	Calibre du câble	CAT6 - 650 MHz
Connecteur(s)		
	Connecteur A	1 - RJ-45
	Connecteur B	1 - RJ-45
Conditions environnementales		
	Température de fonctionnement	-20°C to 80°C (-4°F to 176°F)
	Température de stockage	-20°C to 80°C (-4°F to 176°F)
	Humidité	15 ~ 65%
Caractéristiques physiques		
	Couleur	Rouge
	Calibre du fil	24 AWG
	Type de conducteur	Cuivre torsadé
	Longueur de câble	75.0 ft [22.9 m]
	Longueur du produit	75.0 ft [22.9 m]
	Largeur du produit	0.5 in [1.3 cm]
	Hauteur du produit	0.6 in [1.6 cm]
	Poids du produit	2.1 lb [1.0 kg]
Informations d'emballage		
	Quantité par paquet	1

Longueur du Paquet	11.7 in [29.6 cm]
Largeur du Paquet	9.8 in [24.9 cm]
Hauteur du Paquet	2.2 in [5.5 cm]
Poids brut	2.1 lb [1.0 kg]

Contenu du paquet

Inclus dans le paquet	1 - 75 ft. Cat6 Patch Cable - Red
-----------------------	-----------------------------------

Informations de
garantie

Warranty	À Vie
----------	-------

* L'apparence et les spécifications du produit peuvent être modifiées sans préavis