

7ft CAT6 Ethernet Cable - Red CAT 6 Gigabit Ethernet Wire -250MHz 100W PoE RJ45 UTP Network/Patch Cord Snagless w/Strain Relief Individually Tested

ID del Producto: N6PATCH7RD



This 7-foot Cat6 cable meets or exceeds all Category 6 cable specifications to ensure reliable Gigabit network connections. Plus, the cable features a durable red PVC jacket that enables you to color code your network cable runs as needed.

For easier cable runs, the snagless connectors protect the cable's RJ45 clips during installation, making them less likely to snag or break. This ensures a sturdy connection by preventing the cable from becoming loose from the port.

The cable features molded boots that offer connector strain relief, by stopping the RJ45 connector termination points from bending at sharp angles, and reducing the risk of damage to the cable, which could decrease network performance.

Get the highest value for your cable investment with our Cat 6 cables, each one manufactured using high-quality copper conductors.

Ensure high-performance capability for your demanding Ethernet applications, such as Power-over-Ethernet, using cables that include 24 AWG copper.

Rely on our RJ45 connectors to deliver optimum conductivity while eliminating signal loss due to oxidation or corrosion.

The N6PATCH7RD is backed by StarTech.com's lifetime warranty for guaranteed reliability.

Certificaciones, Reportes y Compatibilidad



Aplicaciones

- Designed for use with Gigabit networks
- Patches from hub to distribution panel
- Connects workstation to wall outlet

Características

- Colored hoods for departmental color coding
- Molded strain relief prevents the cable from being bent at sharp angles at the RJ45 connector, to minimize the stress at the plug termination point
- HIGH PERFORMANCE CAT6 ETHERNET CABLE: 100% copper for error-free Multi Gigabit 1/2.5/5Gbps connections; 10Gbps up to 160'; Individually Tested to comply w/ANSI/TIA-568-2.D Category 6
- POE SUPPORT: 24 AWG stranded copper conductors & UL Rated Wiring (E132276-A) supports up to 100W for PoE devices like VOIP phone & security systems; IEEE 802.3bt & DTE power compliance reduces cable heating
- QUALITY CONSTRUCTION: UL certified wire; 50-micron gold-plated connectors prevent rust/corrosion to avoid costly network downtime; High quality PVC jacket resists bending or fraying damage
- EASY INSTALLATION: 7 foot snagless patch cord for easy installation & flexible disconnection in wiring conduits; Compatible w/Cat5e & earlier standards; Molded boots available for constrained spaces
- SPECS: Length: 7ft (2m) | Color: Red | 250 MHz Rated | Structure: 4 Pair UTP | RJ45 | Jacket: PVC | Wire Gauge: 24 AWG Copper | Wiring: ANSI/T568B | Warranty: Lifetime

Hardware

Política de Garantía	Lifetime
Cantidad de Conductores	4 Pair UTP
Cable Tipo Jacket	PVC - Polyvinyl Chloride
Grado de	Clasificación CMG (uso general)

Inflamabilidad

Estándar de Cableado TIA/EIA-568-B.1-2001 T568B

Rendimiento

Clasificación de Cables CAT6 - 250 MHz

Conector(es)

Conector A 1 - RJ-45

Conector B 1 - RJ-45

Requisitos Ambientales

Temperatura Operativa -20°C to 80°C (-4°F to 176°F)

Temperatura de Almacenamiento -20°C to 80°C (-4°F to 176°F)

Humedad 15 ~ 65%

Características Físicas

Color Rojo

Calibre del Conductor 24 AWG

Tipo de conductor Cobre trenzado

Longitud del Cable 7.0 ft [2.1 m]

Longitud del Producto 7.0 ft [2.1 m]

Peso del Producto 3.6 oz [102 g]

Información de la Caja

Cantidad de Paquetes 1

Longitud de la Caja 6.6 in [16.7 cm]

Ancho de la Caja 7.8 in [19.8 cm]

Altura de la Caja 0.8 in [2.1 cm]

Peso (de la Caja) del 3.8 oz [108.0 g]

Envío

Contenido de la Caja

Incluido en la Caja	1 - 7 ft. Cat6 Patch Cable - Red
---------------------	----------------------------------

Información Acerca de la Garantía

Warranty	De Por Vida
----------	-------------

* La apariencia y las especificaciones del producto están sujetas a cambios sin previo aviso.