

6in CAT6a Ethernet Cable - Blue - Low Smoke Zero Halogen (LSZH) - 10GbE 500MHz
100W PoE++ Snagless RJ-45 w/Strain Reliefs S/FTP Network Patch Cord

Produkt-ID: NLBL-6IN-CAT6A-PATCH



Cat6a Ethernet Low-Smoke Zero-Halogen (LSZH) Shielded cables support Multi-Gigabit/Multi-speed 1/2.5/5Gbps/10Gbp connections. It offers robust protection against electromagnetic interference (EMI/RFI) and noise, ensuring a fast, safe, and reliable network.

LSZH Cat6a Network Cables are more eco-friendly than PVC cables. In the event of a fire, LSZH cables produce low levels of corrosive fumes and smoke. Low levels of acrid combustion pollutants promote increased visibility, resulting in safe and quick building evacuations by staff and first responders.


This high performance Ethernet cable complies with the IEEE 802.3bt-2018 standard. It supports 100W PoE++, providing ample power to Type 4 PoE devices.

The Cat6a cable features snag-less connectors. Snagless molded boots protect the tab/latch on each RJ45 connector. The boots prevent the cable from snagging during cable routing and/or installation into network devices.

The molded boots feature integrated strain reliefs that prevent sharp connector/cable angles at the termination points.

This product is backed for life, including free lifetime 24/5 multi-lingual technical assistance.

Zertifikate Berichte und Kompatibilität



Anwendungen

Merkmale

- **CAT6A ETHERNET CABLE:** High-performance Ethernet Cable for error-free 1/2.5/5/10Gbps multi-gigabit connections; Low Near-End Crosstalk (NEXT) and Return Loss (RL); Individually tested to meet ANSI/TIA-568.2-D standards; Individually Tested/ETL Verified
- **SHIELDED CAT6A CABLE:** Improved signal integrity and protection against noise & electromagnetic (EMI/RFI) interference; Individual twisted pairs wrapped in foil; Outer covering w/ braided shield; Shielded RJ45 connectors with gold-plated pins
- **100W POWER OVER ETHERNET:** 100% stranded copper wire delivers error-free data and stable PoE power, unlike lower quality copper-clad aluminum versions of other brands; Supports PoE devices up to 100W PoE++; Complies with IEEE 802.3bt (Type 4 and lower)
- **DURABLE LSZH JACKET:** PVC Free, Low Smoke Zero Halogen (LSZH) cable jacket produces less dense and corrosive smoke than PVC; Braided construction resists damage from bending
- **SPECS:** Category 6A Network Patch Cord; 6in; Blue; 10Gbps; 500 MHz; 4 Pair S/FTP; Snagless RJ45 with Strain Reliefs; EVA, Al(OH)3; LSZH; 27 AWG; 100% Copper; ETL Verified; ANSI/TIA-568.2-D; Supports Cat6 and earlier standards; Backed for Life

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	4 Pair S/FTP
Typ der Kabelummantelung	Low Smoke Zero Halogen

Leistung

Kabelnennwerte	CAT6a - 500 MHz
----------------	-----------------

Steckverbinder

Steckverbinder A	1 - RJ-45
Steckverbinder B	1 - RJ-45

Umgebungsbedingungen

Betriebstemperatur	0°C to 50°C (32°F to 122°F)
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)

	Feuchtigkeit	0% ~ 85% Relative Luftfeuchtigkeit
Physische Eigenschaften		
	Farbe	Blau
	Drahtstärke	27 AWG (0.361 mm)
	Leitungstyp	Feindrähtiges Kupfer
	Kabellänge	0.5 ft [0.2 m]
	Außendurchmesser des Kabels	0.2 in [5.7 mm]
	Produktlänge	0.5 ft [0.2 m]
	Produktbreite	0.5 in [11.5 mm]
	Produkthöhe	0.5 in [13.9 mm]
	Produktgewicht	0.5 oz [14 g]
Verpackungsinformationen		
	Paketlänge	7.7 in [19.5 cm]
	Paketbreite	8.7 in [22.0 cm]
	Pakethöhe	0.3 in [8.0 mm]
	Versandgewicht (Verpackung)	0.8 oz [23.7 g]
Verpackungsinhalt		
	Im Paket enthalten	1 - Cat6a Ethernet Kabel - LSZH
Garantieinformationen		
	Warranty	Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.