

Portable Laptop Crash Cart Adapter, USB/VGA/Mini DisplayPort KVM Console, File Transfer and Video Capture, TAA Compliant

Product ID: NOTECONS02-VGA-MDP



The USB crash cart adapter gives you control of a headless system, turning your laptop into a portable crash cart for rack servers, PCs, ATMs, kiosks, and more.

Simply connect the laptop crash cart adapter to your computer using the included USB cable, then connect the integrated USB and VGA cables to your server for instant BIOS-level control. Use the included Mini DisplayPort adapter to connect to mDP-enabled computers or servers. With no server-side software required, you can be up and running instantly.

*Please note that the mouse function may be limited in some BIOS/UEFI environments

With the flexible software interface, you can transfer files from your laptop to the server, capture videos for records or instructional purposes, take screenshots and scale the display window to full screen mode or smaller, with no scroll bars helping you to troubleshoot faster.

Powered from the server-side USB connection, the KVM adapter doesn't require an AC outlet so you can connect to any PC that has a VGA or mDP output and USB connection, even if there's no power outlet available.

This pocket-sized adapter features a compact design that easily fits inside your laptop bag and requires no additional accessories to connect, eliminating the need to lug around a large, awkward traditional crash cart to troubleshoot and service your systems.

StarTech.com offers a wide selection of high-quality KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors.

Certifications, Reports and Compatibility



Applications

- ATM and VLT maintenance and repair
- Mobile systems and server repair

Features

- **LAPTOP TO SERVER:** TAA-compliant USB crash cart adapter connects a laptop to a headless system, rack server, PC, ATM, or kiosk, turning it into a portable console; Included Mini DisplayPort adapter adds flexibility for connecting to servers with VGA or mDP
- **EFFICIENT TROUBLESHOOTING:** Easily transfer files, capture screenshots, and log activity using the crash cart adapter software; For optimal performance, install the latest drivers making sure to download the drivers specifically for the NOTECONS02-VGA-MDP
- **BIOS-LEVEL CONTROL:** Connect the crash cart adapter to your laptop using the included USB cable, then connect the integrated USB & VGA cables to your server for instant BIOS-level control; Note: Mouse function may be limited in some BIOS/UEFI environments
- **SELF-POWERED:** KVM adapter is powered by the server-side USB connection, reducing strain on the laptop's battery and eliminating the need for an AC outlet; Ideal for on-site work or tight server rooms where outlets aren't always accessible
- **COMPACT DESIGN:** Lightweight, pocket-sized adapter provides direct system access without relying on a traditional crash cart setup, helping IT technicians perform maintenance without wheeling around a separate monitor, keyboard, and mouse

Hardware

Warranty	2 Years
Audio	No
KVM Ports	1

PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
Video Revision	DisplayPort 1.2
IP Control	No
Hot-Key Selection	No
Maximum Analog Resolutions	1920x1200 @ 60Hz
Maximum Number of Users	1

Connector(s)

Console Interface(s)	1 - USB Mini-B (5 pin)
Host Connectors	1 - VGA (15 pin, High Density D-Sub) 1 - USB 2.0 Type-A (4 pin, 480Mbps)
Other Interface(s)	1 - Mini DisplayPort 1 - VGA (15 pin, High Density D-Sub)

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10, 11 Windows Server 2008 R2, 2012, 2012 R2, 2016, 2019, 2022 macOS 10.9 to 10.15, 11.0, 12.0, 13.0, 14.0, 15.0, 26.1 Linux 2.6 and up - LTS Versions only
------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Special Notes / Requirements

Note	<ul style="list-style-type: none"> - If you're interfacing with a Linux device, this adapter is only compatible with standard QWERTY keyboards in U.S English configuration - Note: Mouse function may be limited or non-functional in some BIOS/UEFI environments
------	--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Indicators

LED Indicators	<ul style="list-style-type: none"> 1 - User Console/USB Link 1 - Host/Server Video (VGA) Link 1 - Host/Server Keyboard/Mouse USB Link
----------------	------------------------------------------------------------------------------------------------------------------------------------------------------------------------

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-40C to 70C (-40F to 158F)
Humidity	80% RH

Physical Characteristics

Color	Black
Material	Plastic
Cable Length	<ul style="list-style-type: none"> 16.4 in [416 mm] 1 x 15in (385mm) USB host cable 1 x 11in (290mm) VGA host cable 1 x 6ft (1.8m) USB Console cable
Weight of Product	7.0 oz [197 g]

Packaging Information

Package Length	11.9 in [30.1 cm]
Package Width	6.5 in [16.5 cm]
Package Height	2.2 in [5.5 cm]
Shipping (Package) Weight	12.6 oz [358.0 g]

What's in the Box

Included in Package	1 - NOTECONS02
	1 - MDP2VGA2
	1 - USB-A to USB Mini-B Cable
	1 - Product Documentation

**Warranty
Information**

Warranty	2 Years
----------	---------

**Product appearance and specifications are subject to change without notice.*

