

USB Crash Cart Adapter with File Transfer & Video Capture

Product ID: NOTECONS02



The USB crash cart adapter gives you control of a headless system, turning your laptop into a portable crash cart for rack servers, PCs, ATMs, kiosks, and more.

Simply connect the laptop crash cart adapter to your computer using the included USB cable, then connect the integrated USB and VGA cables to your server for instant BIOS-level control. With no server-side software required, you can be up and running instantly.

With the flexible software interface, you can transfer files from your laptop to the server, capture videos for records or instructional purposes, take screenshots and scale the display window to full screen mode or smaller, with no scroll bars helping you to troubleshoot faster.

Powered from the server-side USB connection, the KVM adapter doesn't require an AC outlet so you can connect to any PC or device that has a VGA and USB port, even if there's no power outlet available.

This pocket-sized adapter features a compact design that easily fits inside your laptop bag and requires no additional accessories to connect, eliminating the need to lug around a large, awkward traditional crash cart to troubleshoot and service your systems.

StarTech.com offers a wide selection of high-quality KVM-related products to help you access your systems more efficiently without the expense and clutter of extra keyboards, mice and monitors. This USB KVM crash cart adapter is backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- ATM and VLT maintenance and repair

- Mobile systems and server repair

Features

- Access any VGA and USB system directly from your laptop via the KVM console adapter
- Set up quickly with included cables and instant BIOS-level control
- Easily troubleshoot systems with bi-directional file transfers between local and remote computer
- Share troubleshooting information and display errors with video capture at 1920 x 1200 60Hz
- Simple self-powered portability with no external power adapter necessary

Prominence

Warranty	2 Years
Description CDW 75 - 1st Line	StarTech.com USB Crash Cart Adapter with File Transfer & Video Capture

Hardware

Audio	No
KVM Ports	1
PC Interface	USB
PC Video Type	VGA
Number of Monitors Supported	1
Rack-Mountable	No
Cables Included	Yes
Daisy-Chain	No

Performance

On-Screen Display	No
IP Control	No
Hot-Key Selection	No
Maximum Analog Resolutions	1920x1200 @ 60Hz



Maximum Number of Users	1
-------------------------	---

MTBF	909000
------	--------

Connector(s)

Console Interface(s)	USB Mini-B (5 pin)
Host Connectors	VGA (15 pin, High Density D-Sub) USB Type-A (4 pin) USB 2.0

Software

OS Compatibility	Windows XP, Vista, 7, 8, 8.1, 10 Windows Server 2008 R2, 2012, 2012 R2, 2016, 2019 macOS 10.9 to 10.15, 11.0 Linux 2.6 to 4.11 (<i><LTS Versions Only; glibc 2.18 or newer required</i>)
------------------	---

Special Notes / Requirements

Note	If you're interfacing with a Linux device, this adapter is only compatible with standard QWERTY keyboards in U.S English configuration
------	--

Indicators

LED Indicators	User Console/USB Link Host/Server Video (VGA) Link Host/Server Keyboard/Mouse USB Link
----------------	--

Power

Power Source	USB-Powered
--------------	-------------

Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-40C to 70C (-40F to 158F)
Humidity	80% RH

Physical Characteristics

Color	Black
Material	Plastic



Cable Length	16.4 in [41.6 cm]
	1 x 15in (385mm) USB host cable, 1 x 3in (76mm) VGA host cable, 1 x 6ft (1.8m) USB Console cable
Product Length	0.0 in [0.0 mm]
Product Width	2.9 in [74.0 mm]
Product Height	0.6 in [15.0 mm]
Product Depth	4.5 in [11.5 cm]
Weight of Product	6.0 oz [170.0 g]

Packaging Information

Package Length	11.9 in [30.3 cm]
Package Width	6.5 in [16.6 cm]
Package Height	1.8 in [46.0 mm]
Shipping (Package) Weight	12.8 oz [363.0 g]

What's in the Box

Included in Package	USB Crash Cart Adapter
	USB A to Mini-B Cable
	USB Software Key

****Product appearance and specifications are subject to change without notice.***

