

10m (33ft) MTP/MPO Fiber Optic Cable, 12F Type-B, OS2 Single Mode MTP/APC Female Fiber Patch Cable, 9/125m, OFNP Plenum, MTP-12 Fiber Jumper Cord

Product ID: OS2MTP12BOFNP10M



This OS2 MTP/MPO single mode fiber cable supports high-density 40G and 100G connections between switches and servers, helping reduce cable bulk and simplify routing across data hall racks. The 12-fiber design supports high-speed MTP/MPO connectivity for multi-fiber network applications.

Constructed with OS2 9/125m laser-optimized Corning glass, this cable delivers consistent high-bandwidth transmission for long-distance data center and backbone links. Type-B polarity MTP Elite connector maintains proper transmit/receive alignment for multi-lane connections, ensuring reliable performance without additional crossover components. Each cable is individually tested for signal integrity.

The OFNP plenum-rated jacket meets strict fire and low-smoke requirements, making it suitable for routing through air-handling spaces in commercial and enterprise environments, including data center and in-wall pathways.

Designed for use with structured MTP/MPO systems, including multi-fiber trunks, cassettes, and patching setups, this cable supports scalability for growing fiber networks and straightforward migration between 10G, 40G, and 100G infrastructure. The 12-fiber format enables high-density connectivity while reducing overall cable count for cleaner, more efficient installations.

Certifications, Reports and Compatibility



Applications

- Scale your Enterprise and Hyperscale network with high-density MPO/MTP cabling built for 10/40/100G data hall and edge deployment

- Connect QSFP+ and QSFP28 switches, fiber distribution panels, and AI cluster infrastructure with high-density MPO/MTP fiber cabling
- Enable reliable 40GBASE-SR4 and 100GBASE-SR10 parallel optics links for scalable backbone deployments

Features

- **Enable High-Density 100G Deployments:** Support 100G switch uplinks and server connectivity with 12-fiber OS2 MTP/MPO cabling, optimized for scalable 40G/100G fiber architectures in high-density AI cluster interconnects and data hall deployments
- **Rated for Plenum Installations:** Route cabling through overhead and air-handling spaces with an OFNP Plenum-rated jacket designed to meet strict fire and low-smoke requirements; Yellow cable jacket is TIA-standardized for clear identification in single mode fiber deployments
- **Ensure Correct Fiber Polarity:** Type-B MTP Elite connector configuration reverses fiber positions to align transmit and receive paths automatically, supporting reliable QSFP28 high-speed interconnects without additional crossover components
- **Optimize Structured Fiber Infrastructure:** Consolidate multiple OS2 fiber runs into a high-density 12-fiber MTP/MPO backbone made with high quality Corning glass to simplify cable management, improve rack scalability, and support evolving 40G and 100G network architectures
- **The IT Pro's Choice:** Designed for reliability in edge, enterprise, and hyperscale data center deployments, our fiber optic cables are lab-tested and field-proven for seamless integration and maximum uptime; Backed by free lifetime 24/5 multi-lingual technical assistance

General

UPC	065030930512
Warranty	Lifetime

Physical & Environmental

Color	Yellow
Cable Length	393.7 in [10000 mm]
Cable OD	0.1 in [3 mm]
Product Length	393.7 in [10000 mm]
Product Width	0.6 in [14 mm]
Product Height	0.3 in [7 mm]
Weight of Product	3.0 oz [86 g]

Operating Temperature	0C to 70C (32F to 158F)
Storage Temperature	-20C to 70C (-4F to 158F)
Humidity	0~90% RH

Hardware

Fiber Cable Type	Multifiber
Cable Jacket Material	OFNP Plenum Rated
Fiber Size	9/125
Fiber Classification	OS2
Cable Type	Straight-Through

Packaging & In-the-Box

Included in Package	1 - MTP/MPO-12 Fiber Optic Cable
Package Width	9.8 in [250 mm]
Package Depth	11.8 in [300 mm]
Package Height	0.6 in [15 mm]
Shipping (Package) Weight	0.7 oz [19.5 g]

Connector(s)

Connector 1 (Quantity)	1
Connector 1	MPO / MTP Fiber
Connector 2 (Quantity)	1
Connector 2	MPO / MTP Fiber

****Product appearance and specifications are subject to change without notice.***