

2-Port DisplayPort KVM Switch, 4K 60Hz, DP 1.2, EDID Management, 2-Port USB 3.0 Hub, 4x USB HID Ports, TAA Compliant

Product ID: P2AD122-KVM-SWITCH



This DisplayPort KVM Switch enables users to switch between two desktops equipped with USB-A and DisplayPort. It allows sharing of a 4K 60Hz DisplayPort monitor, a keyboard, mouse, two USB 5Gbps devices, a stereo audio output device, and two additional USB 2.0 devices.

The P2AD122-KVM-SWITCH ensures a frictionless switching experience with 4K 60Hz clarity and HDCP-protected content playback. Advanced EDID management and emulation maintain monitor settings across sources, preventing resolution drops, desktop reshuffling, or blank screens when switching. IT teams save time troubleshooting display mismatches, while end-users enjoy uninterrupted workflows for CAD, content creation, and high-end editing.

This universal KVM switch offers hotkey and push-button switching. Hotkeys allow independent switching of audio and video, enabling audio playback from one computer while controlling another. An audible buzzer confirms hotkey inputs, and LEDs provide visual status feedback for the selected host.

The TAA-compliant KVM Switch offers universal compatibility and works with all operating systems, including Windows, macOS, ChromeOS, and Linux. The KVM provides BIOS/UEFI control and is compatible with all hardware platforms, including Intel, AMD, and Apple Silicon (M-Series).

The rugged metal case helps prevent electromagnetic interference (EMI). 4kV Air/4kV Contact ESD protection enhances the reliability and longevity of the KVM. The included set of rubber feet protect the work surface from scratches and keep KVM in place during operation.

Certifications, Reports and Compatibility





Applications

- Share a monitor, mouse, keyboard, and stereo audio peripheral between two desktop computers
- Great for applications like CAD/CAM, video editing, and content creation

Features

- **QUICK SWITCHING 4K 60HZ KVM:** Control two DisplayPort-enabled desktops, workstations, or servers from one mouse, keyboard, USB 5Gbps hub, and 4K 60Hz DisplayPort monitor; Ideal for CAD, video editing, and content creation applications
- **EDID AND CONTENT MANAGEMENT:** Switch between computers without disrupting your screen layout; Built-in EDID management and HDCP support maintain resolution stability, keep icons and windows in place; Ensure protected content streams without interruption
- **UNIVERSAL COMPATIBILITY:** TAA-Compliant KVM Switch provides BIOS control and works with any operating system including Windows, macOS, ChromeOS, and Linux, with no software required; Compatible with all hardware platforms such as Intel, AMD, and Apple
- **MULTIPLE SWITCHING OPTIONS:** Switch between systems using push-buttons or hotkeys with audible confirmation; LED indicators provide at-a-glance port status, while independent audio control lets you monitor audio from one system while managing another
- **DURABLE DESIGN:** Metal housing helps prevent Electro-magnetic Interference (EMI); 4kV Air and 4kV Contact ESD protection enhance the reliability and longevity of the KVM; Included rubber feet protect the work surface and keep KVM in place during operation

Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2
PC Interface	USB 3.2 Gen 1 (5Gbps)
PC Video Type	DisplayPort
Number of Monitors Supported	1
Rack-Mountable	No

	Cables Included	No
Performance		
	On-Screen Display	No
	Video Revision	DisplayPort 1.2
	IP Control	No
	Hot-Key Selection	Yes
	Maximum Data Transfer Rate	5Gbps
	Maximum Cable Length	9.8 ft [3 m]
	Maximum Digital Resolutions	4K 60Hz
	Supported Resolutions	3840 x 2160 60Hz 2560 x 1440 60Hz 1920 x 1080 60Hz Other resolutions and refresh rates may be supported
	Wide Screen Supported	Yes
	Audio Specifications	DisplayPort - 2 Channel Audio Analog Stereo - 2 Channel Audio
	Auto Scan	3, 8, 15 & 30 seconds
	Port Selection Support	Push Button and Hotkeys
	MTBF	130,000 Hours
Connector(s)		
	Console Interface(s)	4 - USB 2.0 Type-A (4 pin, 480Mbps) 2 - USB 3.2 Type-A (9 pin, Gen 1, 5Gbps) 1 - 3.5mm Stereo Female 3 pos 1 - DisplayPort 1 - Barrel Power Connector (Size M, OD:5.50, ID: 2.10)
	Host Connectors	2 - DisplayPort

2 - USB 3.2 Type-B (9 pin, Gen 1, 5Gbps)

2 - 3.5mm Stereo Female 3 pos

Software

OS Compatibility No Drivers or Software Required

Indicators

LED Indicators 2 - Port Selection:
Solid Green - PC 1 ~ 2 connected (powered on)
Solid Red - Selected PC Port

Power

Power Source AC Adapter Included
Input Voltage 100 - 240 AC
Input Current 1.0A
Output Voltage 12V DC
Output Current 3A
Center Tip Polarity Positive
Plug Type M
Power Consumption (In Watts) 36W

Environmental

Operating Temperature 0C to 40C (32F to 104F)
Storage Temperature -20C to 60C (-4F to 140F)
Humidity 0% ~ 80% RH

Physical Characteristics

Color Black
Material Steel
Product Length 6.3 in [160 mm]
Product Width 3.9 in [100 mm]

Product Height 1.6 in [40 mm]

Weight of Product 22.6 oz [640 g]

Packaging Information

Package Length 7.2 in [18.4 cm]

Package Width 9.4 in [23.8 cm]

Package Height 3.5 in [8.9 cm]

Shipping (Package) Weight 5.2 oz [147.0 g]

What's in the Box

Included in Package

- 1 - KVM Switch
- 1 - Set of Rubber Feet
- 1 - Universal Power Adapter (NA/EU/UK/ANZ)
- 1 - Product Documentation

Warranty Information

Warranty 2 Years

****Product appearance and specifications are subject to change without notice.***