

2-Port Dual-Monitor DisplayPort KVM Switch, 4K 60Hz, 2x USB 5Gbps Hub Ports, 2x USB 2.0 HID Ports, Hotkey and Push-Button Switching, TAA Compliant - 3.5mm Audio, HDCP

**Product ID:** P2DD46A2-KVM-SWITCH



This Dual-Monitor KVM Switch enables users to switch between two desktops that are USB-A and DisplayPort enabled. It allows for sharing of dual-4K 60Hz DisplayPort monitors, a keyboard and mouse, and two USB 5Gbps devices.

USB Emulation technology enables faster switching of a keyboard, video, and mouse compared to traditional KVMs. USB Emulation also ensures compatibility with combination keyboards/mice as well as keyboards featuring additional function keys.

This TAA-Compliant KVM Switch supports dual-4K 60Hz DisplayPort monitors, making it ideal for working with high-resolution graphics or video. Additionally, it offers two USB 3.2 Gen 1 (5Gbps) Hub Ports for fast data transfer, and two USB 2.0 HID Ports for the keyboard and mouse. 8kV air and 6kV contact Electrostatic Discharge (ESD) protection.

This Universal KVM Switch provides various switching options, including hotkey or push-button switching. Hotkeys allow for independent switching of USB/Video and Audio, enabling audio playback from one computer while controlling the other. An audible buzzer confirms hotkey input, and LEDs provide a visual status of the selected host.

Developed to improve performance and security, StarTech.com Connectivity Tools is the only software suite on the market that works with a wide range of IT connectivity accessories. The software suite includes:

- Advanced Windows Layout Utility: Setup and save custom windows layouts.
- MAC Address Pass-Through Utility: Improve network security.
- USB Event Monitoring Utility: Track and log connected USB devices.
- Wi-Fi Auto Switch Utility: Enable users to quickly access faster network speeds via wired LAN.

For more information and to download the StarTech.com Connectivity Tools application, please visit: [www.startech.com/connectivity-tools](http://www.startech.com/connectivity-tools)

## Certifications, Reports and Compatibility



## Applications

- Share dual displays, mouse, keyboard, and audio peripherals between two desktop computers
- Great for CAD/CAM, video editing, and content creation applications

## Features

- **FAST SWITCHING:** USB Emulation enables fast switching of a keyboard, video, and mouse between two DisplayPort and USB-A enabled desktops; USB Emulation ensures compatibility with combo keyboards/mice, as well as keyboards featuring additional function keys
- **DUAL 4K 60HZ & USB 5GBPS:** TAA Compliant DisplayPort 1.2 KVM Switch supports up to two 4K 60Hz DisplayPort monitors with two USB 3.2 Gen 1 (5Gbps) Hub Ports and two USB 2.0 HID Ports; Ideal for CAD/CAM, video editing, and content creation applications
- **MULTIPLE SWITCHING OPTIONS:** Universal KVM Switch can be controlled via push-buttons or hotkeys, with an audible buzzer providing confirmation; LEDs provide quick visual port selection status; Listen to audio from one computer, while controlling the other
- **DURABLE DESIGN:** A durable steel housing helps prevent Electro-Magnetic Interference (EMI) enhancing stability and reliability of the KVM; Sturdy construction makes it ideal for installation in a variety of environments; 8kV Air/6kV Contact ESD protection
- **OUR ADVANTAGE:** Included connectivity tools for IT Pro's and IT help-desk support teams with USB Event Monitoring for logging USB device connections with timestamps, and Windows Layout to restore windows locations upon switching hosts

---

### Hardware

Warranty	2 Years
Audio	Yes
KVM Ports	2

PC Interface	USB 3.2 Gen 1 (5Gbps)
PC Video Type	DisplayPort
Number of Monitors Supported	2
Rack-Mountable	No
Cables Included	No
Daisy-Chain	No

---

**Performance**

On-Screen Display	No
Video Revision	DisplayPort 1.2
IP Control	No
Hot-Key Selection	Yes
Maximum Data Transfer Rate	5Gbps
Maximum Cable Length	24.6 ft [7.5 m]
Maximum Digital Resolutions	3840 x 2160 60Hz
Supported Resolutions	3840x2160 @60Hz 2560x1440 @60Hz 1920x1200 @60Hz 1920x1080 @60Hz <i>Other resolutions and refresh rates may be supported</i>
Audio Specifications	DisplayPort - 2 Channel Audio Analog Stereo - 2 Channel Audio
Auto Scan	10, 20, 30, 40, 50, and 60 seconds
Port Selection Support	Push Button and Hotkeys
MTBF	173,052 Hours

---

**Connector(s)**

Console Interface(s)	2 - DisplayPort
----------------------	-----------------

	2 - USB Type-A (9 pin, 5 Gbps)
	2 - USB 2.0 Type-A (4 pin, 480Mbps)
	2 - 3.5mm Stereo Female 3 pos
	1 - Barrel Power Connector (Size N, OD: 5.5, ID: 2.5)
Host Connectors	4 - DisplayPort
	2 - USB 3.2 USB Type-B (9 pin, Gen 1, 5 Gbps)
	4 - 3.5mm Stereo Female 3 pos

---

### Software

OS Compatibility	No Drivers or Software Required
------------------	---------------------------------

---

### Indicators

LED Indicators	2 - PC LED: Solid Green when a host connection is detected. Blinking Green when a host connection is not detected
	2 - Hub LED: Solid Red when the PC port is selected

---

### Power

Power Source	AC Adapter Included
Input Voltage	100 - 240 AC
Input Current	1 A
Output Voltage	12V DC
Output Current	3 A
Center Tip Polarity	Positive
Plug Type	N
Power Consumption (In Watts)	0.1 W

---

### Environmental

Operating Temperature	0C to 40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0% ~ 90% RH (non-condensing)

---

**Physical Characteristics**

Color	Black
Material	Steel
Product Length	6.4 in [16.3 cm]
Product Width	3.9 in [10.0 cm]
Product Height	2.6 in [6.6 cm]
Weight of Product	1.7 lb [0.8 kg]

---

**Packaging Information**

Package Quantity	1
Package Length	6.4 in [16.3 cm]
Package Width	13.0 in [33.1 cm]
Package Height	5.3 in [13.4 cm]
Shipping (Package) Weight	2.8 lb [1.3 kg]

---

**What's in the Box**

Included in Package	1 - KVM Switch
	1 - Universal Power Adapter (NA/JP, EU, UK, NZ)
	1 - Quick-Start Guide

---

***\*Product appearance and specifications are subject to change without notice.***