

1ft (30cm) Power Extension Cord, IEC 60320 C14 to NEMA 5-15R, 10A 125V, 18AWG, 10 Pack, Black Computer Power Extension Cord, AC Outlet Extension Cable for Power Supplies/ PDUs / Network Equipment, UL Listed

Produkt-ID: PAC10010PK



This 10 pack of 1ft long computer power cords enables you to use the switched source on your PC to power your monitors or printers.

Expertly designed and constructed with durable materials, these C14 to NEMA 5-15R cables feature one hooded power plug and one computer power receptacle. They are built with 18 AWG wire and are rated to carry 125V at 10A.

The additional length provided by the monitor power cords allows for cleaner cable management when connecting multiple powered devices.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Ermöglicht die Stromversorgung von Monitor oder Drucker über die geschaltete Quelle am PC

Merkmale

- **AC COMPUTER POWER CORD:** This 1ft (0.3m) 18AWG AC power extension cable with IEC 60320 C14 to NEMA 5-15R connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord made with 100% copper wire | This C14 to 5-15R power extension cord is available in other lengths
- **Ausgelegt für 125 V bei 10 A**
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15R works with North American cables | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Steckverbinder

Garantiebestimmungen	Lifetime
Steckverbinder A	1 - IEC 60320 C14 Strom
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	10 A

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	18 AWG
Kabellänge	1.0 ft [0.3 m]

Produktlänge	12.0 in [30.5 cm]
Produktbreite	1.4 in [3.5 cm]
Produkthöhe	1.0 in [2.5 cm]
Produktgewicht	2.7 oz [76 g]

Verpackungsinformationen

Paketmenge	10
Paketlänge	9.3 in [23.6 cm]
Paketbreite	13.9 in [35.2 cm]
Pakethöhe	2.4 in [6.1 cm]
Versandgewicht (Verpackung)	1.8 lb [0.8 kg]

Verpackungsinhalt

Im Paket enthalten	10 - Computerstromkabel
--------------------	-------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.