

1ft (30cm) Power Extension Cord, IEC 60320 C14 to NEMA 5-15R, 10A 125V, 18AWG, 10 Pack, Black Computer Power Extension Cord, AC Outlet Extension Cable for Power Supplies/ PDUs / Network Equipment, UL Listed

Product ID: PAC10010PK



This 10 pack of 1ft long computer power cords enables you to use the switched source on your PC to power your monitors or printers.

Expertly designed and constructed with durable materials, these C14 to NEMA 5-15R cables feature one hooded power plug and one computer power receptacle. They are built with 18 AWG wire and are rated to carry 125V at 10A.

The additional length provided by the monitor power cords allows for cleaner cable management when connecting multiple powered devices.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to our customers. Our local StarTech.com Technical Advisors have a broad product expertise and work directly with StarTech.com Engineers to provide support for our customers both pre and post-sales.

Certifications, Reports and Compatibility



Applications

- Allows monitor or printer to draw power from the switched source on the PC

Features

- **AC COMPUTER POWER CORD:** This 1ft (0.3m) 18AWG AC power extension cable with IEC 60320 C14 to NEMA 5-15R connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 10A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief connectors for durability Fire Rating: VW-1 3 Conductor extension cord made with 100% copper wire This C14 to 5-15R power extension cord is available in other lengths
- **SPECS:** 1ft (0.3m) AC Power Cord IEC 60320 C14 to NEMA 5-15R 18AWG 125V 10A (Max) Jacket Type: SVT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.24in (6.1mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15R works with North American cables Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Connector(s)

Warranty	Lifetime
Connector A	1 - IEC 60320 C14 Power
Connector B	1 - NEMA 5-15 Power (North America)

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	10 A

Physical Characteristics

Color	Black
Wire Gauge	18 AWG
Cable Length	1.0 ft [0.3 m]
Product Length	12.0 in [30.5 cm]
Product Width	1.4 in [3.5 cm]
Product Height	1.0 in [2.5 cm]
Weight of Product	2.7 oz [76 g]

Packaging Information

Package Quantity	10
Package Length	6.5 in [16.4 cm]
Package Width	11.8 in [29.9 cm]
Package Height	2.7 in [6.9 cm]
Shipping (Package) Weight	1.7 lb [0.8 kg]

What's in the Box

Included in Package	10 - Computer Power Cord
---------------------	--------------------------

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***