

10ft (3m) Power Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

Produkt-ID: PAC10110



This 10-foot Computer Power Cord Extension Cable instantly turns a large, awkward power connector into a smaller, streamlined connector.

The power adapter will fit into any socket, maximizing the space on your power strip, surge protector, or wall outlet.

The power adapter also doubles as a power cord extender, giving you an extra 10ft of reach for your monitor, computer case, or any other powered device.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend an existing power cord by an additional 10ft
- StarTech.com's computer power extension cord saves space and conveniently connects large power adapters so you can maximize all your power/surge strip outlets

Merkmale

- **POWER EXTENSION CORD:** This 10ft (3m) 16AWG AC power extension cable with NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief on connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord with 100% copper wire | This cable is available in other lengths
- **SPECS:** 10ft (3m) AC Power Cord | NEMA 5-15R to NEMA 5-15P | 16AWG | 125V 13A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Typ der Kabelummantelung	PVC - Polyvinyl Chloride

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Strom

Eingangsspannung	125 AC
Eingangsstrom	13 A

Physische Eigenschaften

Farbe	Schwarz
Drahtstärke	16 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]

Produktbreite	0.0 in [0.0 cm]
Produkthöhe	0.0 in [0.0 cm]
Produktgewicht	13.6 oz [384.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	7.6 in [19.2 cm]
Paketbreite	7.6 in [19.4 cm]
Pakethöhe	1.6 in [4.0 cm]
Versandgewicht (Verpackung)	13.6 oz [384.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - 10ft Power Cord Extension - NEMA 5-15R to NEMA 5-15P
--------------------	--

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.