

10ft (3m) Heavy Duty Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 15A 125V, 14AWG, Heavy Gauge Power Extension Cable, NEMA 5-15R to NEMA 5-15P AC Power Cord - UL Listed

Produkt-ID: PAC1011410



The PAC1011410 Computer Power Cord Extension Cable features a heavy gauge wire (14 AWG) that is suitable for handling high power loads, making it a reliable solution for connecting larger servers to PDU (Power Distribution Units).

This 10ft power extension cable extends your existing power connection by 10ft, enabling you to use the PC or another powered device at a greater distance from the power source/outlet.

This high quality replacement Power Extension Cord is backed by our Lifetime Warranty.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend an existing power cord by an additional 10ft
- StarTech.com's computer power extension cord saves space and conveniently connects large power adapters so you can maximize all your power/surge strip outlets

Merkmale

- **HEAVY DUTY EXTENSION CORD:** This 10ft (3m) 14AWG universal power cord with NEMA 5-15R to NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 15A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief on connectors for durability | Fire Rating: VW-1 | 3 Conductor Power cable made with 100% copper wire | Available in other lengths
- **SPECS:** 10ft (3m) AC Power Cord | NEMA 5-15R to NEMA 5-15P | 14AWG | 125V 15A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-15P works with North American outlets | Extend connections to servers, desktop computers, monitors, printers, and more | Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Leistung

Max. Kabellänge	10.0 ft [3.0 m]
-----------------	-----------------

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
Eingangsstrom	15A

Physische
Eigenschaften

Farbe	Schwarz
Drahtstärke	14 AWG
Kabellänge	10.0 ft [3.0 m]
Produktlänge	10.0 ft [3.0 m]
Produktbreite	1.0 in [2.5 cm]
Produkthöhe	1.4 in [3.5 cm]
Produktgewicht	16.9 oz [478.0 g]

Verpackungsinform
ationen

Paketmenge	1
Paketlänge	11.0 in [28.0 cm]
Paketbreite	4.6 in [11.7 cm]
Pakethöhe	2.7 in [6.9 cm]
Versandgewicht (Verpackung)	1.1 lb [0.5 kg]

Verpackungsinhalt

Im Paket enthalten	1 - 10 ft 14 AWG Power Cord Extension - NEMA 5-15R to NEMA 5-15P
--------------------	--

Garantieinformatio
nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.