

3ft (1m) Power Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

Produkt-ID: PAC1013



The PAC1013 power extension cord extends your existing power connection by up to 3ft.

The added cable distance allows you to minimize clutter, giving you more room for additional connections on your power strip, surge protector or wall outlet.

Designed for durability and dependability, this NEMA extension cord is backed by our Lifetime Warranty.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Extend the connection distance between your PC, Monitor, Laser Printer or Scanner and your power strip, surge protector or wall outlet by up to 3 ft

## Merkmale

- POWER EXTENSION CORD: This 3ft (1m) 16AWG AC power extension cable with NEMA 5-15R and

NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 13A

- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief on connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord with 100% copper wire | This cable is available in other lengths
- **SPECS:** 3ft (1m) AC Power Cord | NEMA 5-15R to NEMA 5-15P | 16AWG | 125V 13A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

#### Hardware

|                          |                          |
|--------------------------|--------------------------|
| Garantiebestimmungen     | Lifetime                 |
| Anzahl von Leitern       | 3                        |
| Typ der Kabelummantelung | PVC - Polyvinyl Chloride |
| Kabeltyp                 | SJT                      |

#### Steckverbinder

|                  |                                   |
|------------------|-----------------------------------|
| Steckverbinder A | 1 - NEMA 5-15 Strom (Nordamerika) |
| Steckverbinder B | 1 - NEMA 5-15 Strom (Nordamerika) |

#### Spezielle Hinweise/Anforderungen

|         |           |
|---------|-----------|
| Hinweis | UL Listed |
|---------|-----------|

#### Strom

|                  |        |
|------------------|--------|
| Eingangsspannung | 125 AC |
| Eingangsstrom    | 13 A   |

#### Physische Eigenschaften

|       |         |
|-------|---------|
| Farbe | Schwarz |
|-------|---------|

|                |                   |
|----------------|-------------------|
| Drahtstärke    | 16 AWG            |
| Kabellänge     | 3.0 ft [0.9 m]    |
| Produktlänge   | 36.0 in [91.4 cm] |
| Produktbreite  | 1.0 in [2.5 cm]   |
| Produkthöhe    | 1.4 in [3.6 cm]   |
| Produktgewicht | 5.2 oz [147.0 g]  |

---

#### Verpackungsinformationen

|                             |                  |
|-----------------------------|------------------|
| Paketmenge                  | 1                |
| Paketlänge                  | 6.5 in [16.4 cm] |
| Paketbreite                 | 2.7 in [6.9 cm]  |
| Pakethöhe                   | 2.3 in [5.9 cm]  |
| Versandgewicht (Verpackung) | 5.5 oz [156.0 g] |

---

#### Verpackungsinhalt

|                    |                                                         |
|--------------------|---------------------------------------------------------|
| Im Paket enthalten | 1 - 3ft Power Cord Extension - NEMA 5-15R to NEMA 5-15P |
|--------------------|---------------------------------------------------------|

---

#### Garantieinformationen

|          |          |
|----------|----------|
| Warranty | Lifetime |
|----------|----------|

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.