

1ft (30cm) Short Extension Cord, NEMA 5-15R to NEMA 5-15P Black Extension Cord, 13A 125V, 16AWG, Outlet Extension Power Cable, NEMA 5-15R to NEMA 5-15P AC Computer Power Cord - UL Listed

Produkt-ID: PAC101



This 12in Computer Power Cord Extension Cable instantly turns a large, awkward power connector into a smaller, streamlined connector.

The power adapter will fit into any socket, maximizing the space on your power strip, surge protector, or wall outlet.

The power adapter also doubles as a power cord extender, giving you an extra 12in of reach for your monitor, computer case, or any other powered device.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Allows you to attach bulky power adapter to a power strip or a wall outlet without blocking other outlets
- StarTech.com's power extender cable saves space and conveniently connects big sized adapters so you can maximize all your power/surge strip outlets

Merkmale

- **POWER EXTENSION CORD:** This 1ft (0.3m) 16AWG AC power extension cable with NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office - Indoor use - Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) - Fully molded strain relief on connectors for durability - Fire Rating: VW-1 - 3 Conductor extension cord with 100% copper wire - This cable is available in other lengths
- **SPECS:** 1ft (0.3m) AC Power Cord - NEMA 5-15R to NEMA 5-15P - 16AWG - 125V 13A (Max) - Jacket Type: SJT - Jacket Material: PVC - Black - Temperature Range: 37°F to 140°F (3°C to 60°C) - Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets - Extend a 3-prong power connection from your desktop computer, server, or printer - Replacement power supply cable/cord
- **DIE BEVORZUGTE WAHL DES IT-PROFIS:** Entwickelt und erstellt für Computerfachleute, ist dieser Stromkabel Lebenslang unterstützt, inklusive kostenlosem, lebenslangem, mehrsprachigem technischem Kundendienst (24/5).

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Strom

Eingangsspannung	125 AC
Eingangsstrom	13 A

Umgebungsbedingungen

Betriebstemperatur	-20°C to 60°C (-4°F to 140°F)
--------------------	-------------------------------

Physische
Eigenschaften

Farbe	Schwarz
Drahtstärke	16 AWG
Kabellänge	12.0 in [304.8 mm]
Produktlänge	12.0 in [30.5 cm]
Produktbreite	1.0 in [2.5 cm]
Produkthöhe	2.1 in [5.5 cm]
Produktgewicht	3.0 oz [86.0 g]

Verpackungsinform
ationen

Paketmenge	1
Paketlänge	5.5 in [14.0 cm]
Paketbreite	7.8 in [19.8 cm]
Pakethöhe	1.1 in [2.8 cm]
Versandgewicht (Verpackung)	4.9 oz [138.0 g]

Garantieinformatio
nen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.