

1ft (30cm) Power Extension Cord, Right Angle NEMA 5-15P to NEMA 5-15R, 13A 125V, 16AWG, Black Computer Power Extension Cord, AC Outlet Extension Cable, UL Listed

Produkt-ID: PAC101R1



Save room around the office, maximize power outlet space, and extend the length of your bulky power cords. This flat extension cord lets you do all three.

The low-profile extension cord has a right-angled NEMA 5-15 plug that sits flat against the wall. This lets you save clearance room when plugging in your device behind a cabinet, desk or other piece of furniture. You no longer need to push up against the plug so that your furniture isn't sticking off the wall. This avoids putting strain on the plug and protects it from damage. You can use it to extend any NEMA 5-15 power cord (computer, TV, office lamp, etc.) that needs to be plugged into a power outlet located behind a piece of furniture.

The right-angle power cord also lets you maximize the space on your power strip, surge protector or wall outlet. Since the plug sits to the right of the outlet, the outlet below it or above it isn't blocked which comes in handy when you have to plug in a device with a large, bulky power cord. You can plug the bulky power cord into the receptacle of the extension cord and plug the right-angled plug into the outlet, freeing up another outlet that would have otherwise been blocked.

PAC101R1 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend an existing power cord by up to a foot

Merkmale

- **AC POWER EXTENSION CORD:** This 1ft (0.3m) Right-Angle 16AWG AC power extension cord with NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord made with 100% copper wire | This power extension cord is available in other lengths
- **SPECS:** 1ft (0.3m) AC Power Cord | NEMA 5-15R to Right-Angle NEMA 5-15P | 16AWG | 125V 13A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Anzahl von Leitern	3
Typ der Kabelummantelung	PVC - Polyvinyl Chloride
Kabeltyp	SJT

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	1 - NEMA 5-15 Strom (Nordamerika)

Spezielle Hinweise/Anforderungen

Hinweis	UL Listed
---------	-----------

Strom

Eingangsspannung	125 AC
------------------	--------

Eingangsstrom		13 A
Umgebungsbedingungen		
Betriebstemperatur	-20°C to 60°C (-4°F to 140°F)	
Lagertemperatur	-20°C to 60°C (-4°F to 140°F)	
Feuchtigkeit	20~80% RH	
Physische Eigenschaften		
Farbe	Schwarz	
Steckverbinderart	Gerade auf rechtsgewinkelt	
Drahtstärke	16 AWG	
Kabellänge	1.0 ft [0.3 m]	
Produktlänge	12.0 in [30.5 cm]	
Produktbreite	1.0 in [2.6 cm]	
Produkthöhe	1.4 in [3.5 cm]	
Produktgewicht	3.5 oz [98.0 g]	
Verpackungsinformationen		
Paketmenge	1	
Paketlänge	5.3 in [13.4 cm]	
Paketbreite	7.9 in [20.0 cm]	
Pakethöhe	1.3 in [3.2 cm]	
Versandgewicht (Verpackung)	3.7 oz [104.0 g]	
Verpackungsinhalt		
Im Paket enthalten	1 - power cable	
Garantieinformatio		

nen

Warranty

Lifetime

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.