

Flat Extension Cord - NEMA 5-15R to NEMA Right-Angle 5-15P - 1 ft.

Product ID: PAC101R1



Save room around the office, maximize power outlet space, and extend the length of your bulky power cords. This flat extension cord lets you do all three.

The low-profile extension cord has a right-angled NEMA 5-15 plug that sits flat against the wall. This lets you save clearance room when plugging in your device behind a cabinet, desk or other piece of furniture. You no longer need to push up against the plug so that your furniture isn't sticking off the wall. This avoids putting strain on the plug and protects it from damage. You can use it to extend any NEMA 5-15 power cord (computer, TV, office lamp, etc.) that needs to be plugged into a power outlet located behind a piece of furniture.

The right-angle power cord also lets you maximize the space on your power strip, surge protector or wall outlet. Since the plug sits to the right of the outlet, the outlet below it or above it isn't blocked which comes in handy when you have to plug in a device with a large, bulky power cord. You can plug the bulky power cord into the receptacle of the extension cord and plug the right-angled plug into the outlet, freeing up another outlet that would have otherwise been blocked.

PAC101R3 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

Certifications, Reports and Compatibility

Applications

- Extend an existing power cord by up to a foot

Features

- Position your furniture close to the wall

- Maximize space on your power strip, surge protector or wall outlet
- Replace a bulky power plug with this right-angled plug
- Rated to carry 125V at 13A

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	NEMA 5-15 Power (North America)
Connector B	NEMA 5-15 Power (North America)

Special Notes / Requirements

Note	UL Listed
------	-----------

Power

Input Voltage	125 AC
Input Current	13 A

Environmental

Operating Temperature	-20C to 60C (-4F to 140F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	20~80% RH

Physical Characteristics

Color	Black
Connector Style	Straight to Right Angle
Wire Gauge	16 AWG
Cable Length	12.0 in [30.5 cm]
Product Length	12.0 in [30.5 cm]



Product Width	0.5 in [12.0 mm]
Product Height	0.4 in [10.0 mm]
Weight of Product	3.5 oz [98.0 g]

Packaging Information

Package Length	8.8 in [22.4 cm]
Package Width	7.8 in [19.8 cm]
Package Height	0.4 in [10.0 mm]
Shipping (Package) Weight	3.5 oz [100.0 g]

What's in the Box

Included in Package	power cable
---------------------	-------------

**Product appearance and specifications are subject to change without notice.*

