

3ft (1m) Power Extension Cord, Right Angle NEMA 5-15P to NEMA 5-15R, 13A 125V, 16AWG, Black Computer Power Extension Cord, Flat Extension Cord, AC Outlet Extension Cable, UL Listed

Produkt-ID: PAC101R3



Save room around the office, maximize power outlet space, and extend the length of your bulky power cords. This flat extension cord lets you do all three.

The low-profile extension cord has a right-angled NEMA 5-15 plug that sits flat against the wall. This lets you save clearance room when plugging in your device behind a cabinet, desk or other piece of furniture. You no longer need to push up against the plug so that your furniture isn't sticking off the wall. This avoids putting strain on the plug and protects it from damage. You can use it to extend any NEMA 5-15 power cord (computer, TV, office lamp, etc.) that needs to be plugged into a power outlet located behind a piece of furniture.

The right-angle power cord also lets you maximize the space on your power strip, surge protector or wall outlet. The plug sits to the right of the outlet, so the outlet below it or above it isn't blocked, which comes in handy when you have to plug in a device with a large, bulky power cord. You can plug the bulky power cord into the receptacle of the extension cord and plug the right-angled plug into the outlet, freeing up another outlet that would have otherwise been blocked.

PAC101R3 is backed by a StarTech.com lifetime warranty for guaranteed reliability.

## Zertifikate Berichte und Kompatibilität



## Anwendungen

- Extend an existing power cord by up to 3 feet

## Merkmale

- **AC POWER EXTENSION CORD:** This 3ft (0.9m) Right-Angle 16AWG AC power extension cable with NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) | Fully molded strain relief connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord made with 100% copper wire | This power extension cord is available in other lengths
- **SPECS:** 3ft (0.9m) AC Power Cord | NEMA 5-15R to Right-Angle NEMA 5-15P | 16AWG | 125V 13A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

### Hardware

|                          |                          |
|--------------------------|--------------------------|
| Garantiebestimmungen     | Lifetime                 |
| Anzahl von Leitern       | 3                        |
| Typ der Kabelummantelung | PVC - Polyvinyl Chloride |
| Kabeltyp                 | SJT                      |

### Steckverbinder

|                  |                                   |
|------------------|-----------------------------------|
| Steckverbinder A | 1 - NEMA 5-15 Strom (Nordamerika) |
| Steckverbinder B | 1 - NEMA 5-15 Strom (Nordamerika) |

### Spezielle Hinweise/Anforderungen

|         |           |
|---------|-----------|
| Hinweis | UL Listed |
|---------|-----------|

## Strom

|                  |        |
|------------------|--------|
| Eingangsspannung | 125 AC |
| Eingangsstrom    | 13 A   |

## Umgebungsbedingungen

|                    |                               |
|--------------------|-------------------------------|
| Betriebstemperatur | -20°C to 60°C (-4°F to 140°F) |
| Lagertemperatur    | -20°C to 60°C (-4°F to 140°F) |
| Feuchtigkeit       | 20~80% RH                     |

## Physische Eigenschaften

|                   |                            |
|-------------------|----------------------------|
| Farbe             | Schwarz                    |
| Steckverbinderart | Gerade auf rechtsgewinkelt |
| Drahtstärke       | 16 AWG                     |
| Kabellänge        | 3.0 ft [0.9 m]             |
| Produktlänge      | 36.0 in [91.4 cm]          |
| Produktbreite     | 0.5 in [1.2 cm]            |
| Produkthöhe       | 0.4 in [1.0 cm]            |
| Produktgewicht    | 5.7 oz [162 g]             |

## Verpackungsinformationen

|                             |                  |
|-----------------------------|------------------|
| Paketmenge                  | 1                |
| Paketlänge                  | 9.0 in [22.8 cm] |
| Paketbreite                 | 3.1 in [8.0 cm]  |
| Pakethöhe                   | 2.2 in [5.7 cm]  |
| Versandgewicht (Verpackung) | 6.1 oz [172.0 g] |

## Verpackungsinhalt

|                    |                 |
|--------------------|-----------------|
| Im Paket enthalten | 1 - power cable |
|--------------------|-----------------|

---

Garantieinformationen

Warranty

Lifetime

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.