

3ft (1m) Piggyback Power Extension Cord - NEMA 5-15P to 2x NEMA 5-15R, 16 AWG, 125V/15A - UL Certified - 1 to 2 Outlet Saver Extension Cord - 3-Prong Electrical Power Cable

Produkt-ID: PAC1023



This 3 ft Power Extension Cord turns large power connectors into a single smaller, streamlined connector. Featuring two NEMA 5 15R to one NEMA 5 15P, the electrical extension cord maximizes the available space on your power strip, surge protector, or wall outlet.

This pass through extension cord with multiple outlets allows you to connect up to two power adapters to a single outlet, providing additional connectivity for powered devices beyond what your power socket would normally offer.

This 3 foot power cable provides additional length for connecting your powered devices, allowing for cleaner cable management.

Reduce the strain on your wall outlets by connecting heavier power adapters through this 16 AWG piggyback extension cord.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

PAC1023 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



## Anwendungen

- Extend the connection distance between your PC, monitor, laser printer or scanner

## Merkmale

- **1 TO 2 OUTLET:** The 3 prong piggyback extension cord offers an extra female NEMA 5-15 that allows you to power two devices using one power outlet; Provides an economical solution where there are not enough power outlets available for your equipment
- **FREE UP OUTLET SPACE:** With this 3ft extension cable you can attach bulky power adapters or maximize space on power bars without blocking or interfering with other outlets
- **OUTLET SAVER:** This 3ft male to female electrical extension cord can reduce wear and tear usage for power outlets; The power cable can help relieve stress and protect wall outlets from damage; Ideal for use in places where repeated connection is required
- **DURABLE AND SAFETY CERTIFIED:** Long lasting PVC connectors that are designed to withstand everyday use; PVC jacket w/ flexible strain relief prevents cable from fraying or damage; UL certified to ensure maximum safety for devices and provide reliable power
- **SPECS:** Length: 3 foot | NEMA 5-15P (Plug) to 2x NEMA 5-15R (Receptacle) | 16AWG | 125 V, 15 A (Max) | UL Certified | Cable OD: 0.33" | Jacket: PVC | Color: Black | Lifetime Warranty

---

### Hardware

|                          |                          |
|--------------------------|--------------------------|
| Garantiebestimmungen     | Lifetime                 |
| Anzahl von Leitern       | 3                        |
| Typ der Kabelummantelung | PVC - Polyvinyl Chloride |
| Kabeltyp                 | SJT                      |

---

### Steckverbinder

|                  |                                   |
|------------------|-----------------------------------|
| Steckverbinder A | 1 - NEMA 5-15 Strom (Nordamerika) |
| Steckverbinder B | 2 - NEMA 5-15 Strom (Nordamerika) |

---

### Strom

|                  |        |
|------------------|--------|
| Eingangsspannung | 125 AC |
| Eingangsstrom    | 15 A   |

---

#### Umgebungsbedingungen

|                    |                               |
|--------------------|-------------------------------|
| Betriebstemperatur | 0°C to +40°C (32°F to 104°F)  |
| Lagertemperatur    | -20°C to 60°C (-4°F to 140°F) |
| Feuchtigkeit       | 0% to 90% RH                  |

---

#### Physische Eigenschaften

|                   |                  |
|-------------------|------------------|
| Farbe             | Schwarz          |
| Steckverbinderart | Gerade           |
| Drahtstärke       | 16 AWG           |
| Kabellänge        | 3.0 ft [0.9 m]   |
| Produktlänge      | 3.4 ft [1.0 m]   |
| Produktbreite     | 2.6 in [6.5 cm]  |
| Produkthöhe       | 1.2 in [3.0 cm]  |
| Produktgewicht    | 7.1 oz [200.0 g] |

---

#### Verpackungsinformationen

|                             |                  |
|-----------------------------|------------------|
| Paketmenge                  | 1                |
| Paketlänge                  | 6.8 in [17.2 cm] |
| Paketbreite                 | 3.5 in [8.9 cm]  |
| Pakethöhe                   | 1.9 in [4.8 cm]  |
| Versandgewicht (Verpackung) | 0.1 oz [2.0 g]   |

---

#### Verpackungsinhalt

|                    |                                                               |
|--------------------|---------------------------------------------------------------|
| Im Paket enthalten | 1 - 1 m Netzverlängerungskabel - NEMA515-P auf 2 x NEMA 5-15R |
|--------------------|---------------------------------------------------------------|

---

Garantieinformatio  
nen

Warranty

Lifetime

---

\* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.