

3ft (1m) Piggyback Power Extension Cord - NEMA 5-15P to 2x NEMA 5-15R, 16 AWG, 125V/15A - UL Certified - 1 to 2 Outlet Saver Extension Cord - 3-Prong Electrical Power Cable

Product ID: PAC1023



This 3 ft Power Extension Cord turns large power connectors into a single smaller, streamlined connector. Featuring two NEMA 5 15R to one NEMA 5 15P, the electrical extension cord maximizes the available space on your power strip, surge protector, or wall outlet.

This pass through extension cord with multiple outlets allows you to connect up to two power adapters to a single outlet, providing additional connectivity for powered devices beyond what your power socket would normally offer.

This 3 foot power cable provides additional length for connecting your powered devices, allowing for cleaner cable management.

Reduce the strain on your wall outlets by connecting heavier power adapters through this 16 AWG piggyback extension cord.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

PAC1023 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Extend the connection distance between your PC, monitor, laser printer or scanner

Features

- **1 TO 2 OUTLET:** The 3 prong piggyback extension cord offers an extra female NEMA 5-15 that allows you to power two devices using one power outlet; Provides an economical solution where there are not enough power outlets available for your equipment
- **FREE UP OUTLET SPACE:** With this 3ft extension cable you can attach bulky power adapters or maximize space on power bars without blocking or interfering with other outlets
- **OUTLET SAVER:** This 3ft male to female electrical extension cord can reduce wear and tear usage for power outlets; The power cable can help relieve stress and protect wall outlets from damage; Ideal for use in places where repeated connection is required
- **DURABLE AND SAFETY CERTIFIED:** Long lasting PVC connectors that are designed to withstand everyday use; PVC jacket w/ flexible strain relief prevents cable from fraying or damage; UL certified to ensure maximum safety for devices and provide reliable power
- **SPECS:** Length: 3 foot NEMA 5-15P (Plug) to 2x NEMA 5-15R (Receptacle) 16AWG 125 V, 15 A (Max) UL Certified Cable OD: 0.33" Jacket: PVC Color: Black Lifetime Warranty

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	2 - NEMA 5-15 Power (North America)

Power

Input Voltage	125 AC
Input Current	15 A

Environmental

Operating Temperature	0C to +40C (32F to 104F)
Storage Temperature	-20C to 60C (-4F to 140F)
Humidity	0% to 90% RH

Physical Characteristics

Color	Black
Connector Style	Straight
Wire Gauge	16 AWG
Cable Length	3.0 ft [0.9 m]
Product Length	3.4 ft [1.0 m]
Product Width	2.6 in [6.5 cm]
Product Height	1.2 in [3.0 cm]
Weight of Product	7.1 oz [200.0 g]

Packaging Information

Package Quantity	1
Package Length	6.8 in [17.2 cm]
Package Width	3.5 in [8.9 cm]
Package Height	1.9 in [4.8 cm]
Shipping (Package) Weight	0.1 oz [2.0 g]

What's in the Box

Included in Package	1 - 3 ft. Power Cord Extension - NEMA515-P to 2 x NEMA 5-15R
---------------------	--

Warranty Information

Warranty	Lifetime
----------	----------

**Product appearance and specifications are subject to change without notice.*