

1ft (30cm) Short Extension Cord, NEMA 5-15P/R to NEMA 5-15R, 13A 125V, 16AWG, Black, Outlet Saver Power Extension Cord with Extra Passthrough Outlet, AC Extension Cable, UL Listed

Produkt-ID: PAC102



This twelve inch outlet saver extension cord instantly turns two larger power connectors into a single smaller, streamlined connector. The short extension cord with two NEMA 5 15 outlets maximizes the available space on your power strip, surge protector, or wall outlet.

The additional length provided by this one foot cord allows for cleaner cable management when connecting multiple powered devices.

Reduce the strain on your wall outlets by connecting heavier power adapters through this 16 AWG 3 prong outlet extender.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

PAC102 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Zertifikate Berichte und Kompatibilität



Anwendungen

- Extend the connection distance between your PC, monitor, laser printer or scanner

Merkmale

- **AC POWER EXTENSION CORD:** This 12in (0.3m) 16AWG AC power extension cable with 2x NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office | Indoor use | Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62) | Fully molded strain relief on connectors for durability | Fire Rating: VW-1 | 3 Conductor extension cord with 100% copper wire | This cable is available in other lengths
- **SPECS:** 12in (0.3m) AC Power Cord | 2x NEMA 5-15R to NEMA 5-15P | 16AWG | 125V 13A (Max) | Jacket Type: SJT | Jacket Material: PVC | Black | Temperature Range: 37°F to 140°F (3°C to 60°C) | Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets | Extend a 3-prong power connection from your desktop computer, server, or printer | Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Garantiebestimmungen	Lifetime
Typ der Kabelummantelung	PVC - Polyvinyl Chloride

Steckverbinder

Steckverbinder A	1 - NEMA 5-15 Strom (Nordamerika)
Steckverbinder B	2 - NEMA 5-15 Strom (Nordamerika)

Strom

Eingangsspannung	125 AC
Eingangsstrom	13 A

Physische Eigenschaften

Farbe	Schwarz
-------	---------

Drahtstärke	16 AWG
Kabellänge	12.0 in [30.5 cm]
Produktlänge	12.0 in [30.5 cm]
Produktbreite	1.7 in [4.3 cm]
Produkthöhe	1.4 in [3.5 cm]
Produktgewicht	4.2 oz [118.0 g]

Verpackungsinformationen

Paketmenge	1
Paketlänge	6.0 in [15.2 cm]
Paketbreite	5.6 in [14.2 cm]
Pakethöhe	1.5 in [3.8 cm]
Versandgewicht (Verpackung)	4.3 oz [122.0 g]

Verpackungsinhalt

Im Paket enthalten	1 - Power Cord Extension
--------------------	--------------------------

Garantieinformationen

Warranty	Lifetime
----------	----------

* Größe, Aussehen und Spezifikationen sind Änderungen ohne vorherige Ankündigung vorbehalten.