

1ft (30cm) Short Extension Cord, NEMA 5-15P/R to NEMA 5-15R, 13A 125V, 16AWG, Black, Outlet Saver Power Extension Cord with Extra Passthrough Outlet, AC Extension Cable, UL Listed

Product ID: PAC102



This twelve inch outlet saver extension cord instantly turns two larger power connectors into a single smaller, streamlined connector. The short extension cord with two NEMA 5 15 outlets maximizes the available space on your power strip, surge protector, or wall outlet.

The additional length provided by this one foot cord allows for cleaner cable management when connecting multiple powered devices.

Reduce the strain on your wall outlets by connecting heavier power adapters through this 16 AWG 3 prong outlet extender.

StarTech.com conducts thorough compatibility and performance testing on all our products to ensure we are meeting or exceeding industry standards and providing high-quality products to IT Professionals. Our local StarTech.com Technical Advisors have broad product expertise and work directly with our StarTech.com Engineers to provide support for our customers both pre and post-sales.

PAC102 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Extend the connection distance between your PC, monitor, laser printer or scanner

Features

- **AC POWER EXTENSION CORD:** This 12in (0.3m) 16AWG AC power extension cable with 2x NEMA 5-15R and NEMA 5-15P connectors is suitable for workstations/home office Indoor use Rated to carry 125V at 13A
- **PERFORMANCE AND SAFETY:** UL listed (UL62) Fully molded strain relief on connectors for durability Fire Rating: VW-1 3 Conductor extension cord with 100% copper wire This cable is available in other lengths
- **SPECS:** 12in (0.3m) AC Power Cord 2x NEMA 5-15R to NEMA 5-15P 16AWG 125V 13A (Max) Jacket Type: SJT Jacket Material: PVC Black Temperature Range: 37F to 140F (3C to 60C) Cable Outer Diameter: 0.33in (8.5mm)
- **COMPATIBILITY:** PC Power Extension Cord NEMA 5-15P works with North American outlets Extend a 3-prong power connection from your desktop computer, server, or printer Replacement power supply cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this extension cord is backed for life, including free lifetime 24/5 multi-lingual technical assistance

Hardware

Warranty	Lifetime
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA 5-15 Power (North America)
Connector B	2 - NEMA 5-15 Power (North America)

Power

Input Voltage	125 AC
Input Current	13 A

Physical Characteristics

Color	Black
Wire Gauge	16 AWG
Cable Length	12.0 in [30.5 cm]
Product Length	12.0 in [30.5 cm]
Product Width	1.7 in [4.3 cm]
Product Height	1.4 in [3.5 cm]

Weight of Product	4.2 oz [118.0 g]
-------------------	------------------

Packaging Information

Package Quantity	1
Package Length	6.0 in [15.2 cm]
Package Width	5.6 in [14.2 cm]
Package Height	1.5 in [3.8 cm]
Shipping (Package) Weight	4.3 oz [122.0 g]

What's in the Box

Included in Package	1 - Power Cord Extension
---------------------	--------------------------

**Product appearance and specifications are subject to change without notice.*