

3ft (1m) Heavy Duty Extension Cord, NEMA L5-20R to NEMA 5-20P Black Extension Cord, 13A 125V, 12AWG, Heavy Gauge Power Extension Cable, NEMA L5-20R to NEMA 5-20P AC Power Cord - UL Listed

Product ID: PAC520PLR3



This 3 ft. Power Adapter Cord features NEMA-L5-20R to NEMA-5-20P connectors, creating a high-power 20A connection for your Power Distribution Units.

Featuring a twist locking NEMA-L5-20 receptacle and a NEMA-5-20P plug, this external power cable ensures your equipment is securely connected to avoid accidental power loss or downtime. Built with a 12 AWG wire, the heavy-duty adapter provides a high-power connection to support your server room equipment or large server applications.

This three-foot extension cord provides additional length for connecting your powered devices, allowing for cleaner cable management.

Constructed with high quality materials, the NEMA power cable has fully molded strain relief connectors providing a dependable connection.

PAC520PLR3 is backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility



Applications

- Connect large servers to PDUs, even in high-temperature environments

Features

- **HEAVY DUTY EXTENSION CORD:** This 3ft (1m) 12AWG universal power cord with NEMA-L5-20R to NEMA-5-20P connectors is suitable for servers or other high-powered equipment Indoor use Rated to carry 125V at 20A
- **PERFORMANCE AND SAFETY:** UL listed (UL62 & UL817) Fully molded strain relief on connectors for durability
Fire Rating: VW-1 3 Conductor Power cable made with 100% copper wire Available in other lengths
- **SPECS:** 3ft (1m) AC Power Cord NEMA-L5-20R to NEMA-5-20P 12AWG 125V 20A (Max) Jacket Type: SJT
Jacket Material: PVC Black Temperature Range: 37F to 227F (3C to 105C) Cable Outer Diameter: 0.36in (9.14mm)
- **COMPATIBILITY:** PC Power Cord NEMA 5-20P works with North American outlets Extend connections to servers, desktop computers, monitors, printers, and more Replacement power extension cable/cord
- **THE IT PRO'S CHOICE:** Designed and built for IT Professionals, this power extension cable is backed for life, including free lifetime 24/5 multilingual technical assistance

Hardware

Warranty	Lifetime
Number of Conductors	3
Cable Jacket Material	PVC - Polyvinyl Chloride
Cable Type	SJT

Connector(s)

Connector A	1 - NEMA L5-20 Power (North America, Locking)
Connector B	1 - NEMA L5-20 Power (North America, Locking)

Power

Input Voltage	125 AC
Input Current	13 A

Environmental

Operating Temperature	0C to 50C (32F to 122F)
-----------------------	-------------------------

Physical Characteristics

Color	Black
Wire Gauge	12 AWG
Cable Length	3.0 ft [0.9 m]

Product Length	36.0 in [91.5 cm]
Product Width	1.6 in [4.0 cm]
Product Height	1.6 in [4.0 cm]
Weight of Product	10.5 oz [298.0 g]

Packaging Information

Package Quantity	1
Package Length	7.4 in [18.8 cm]
Package Width	7.0 in [17.7 cm]
Package Height	1.7 in [4.3 cm]
Shipping (Package) Weight	11.0 oz [312.0 g]

What's in the Box

Included in Package	1 - Power Adapter Cord
---------------------	------------------------

Warranty Information

Warranty	Lifetime
----------	----------

****Product appearance and specifications are subject to change without notice.***