

24 Port 0.5U Cat5e Patch Panel - RJ45 Ethernet Rackmount Cat 5e 110 Patch Panel

Product ID: PANELHU24



The PANELHU24 Rack Mount Cat5e patch panel condenses 24 ports into a 0.5U panel, making it an ideal solution for smaller installations.

Color coded for both T568A and T568B wiring, this network patch panel provides the perfect solution for any voice or LAN application and offers dual type IDC termination. For convenience, the port numbers are clearly marked on the front of each RJ45 port, offering a quick and easy way to identify cable runs.

Durably constructed of only top quality materials, this 24-port Ethernet patch panel is backed by StarTech.com's 2 year warranty.

Certifications, Reports and Compatibility

Applications

- For installation in 19" rack/cabinets
- Suitable for applications that use 22-26 AWG solid state and standard network cables
- 1000BASE-T Gigabit Ethernet, 100BASE-TX Fast Ethernet, 10BASE-T Ethernet applications
- Voice, video and other applications

Features

- High impact plastic housing, flame retardant UL 94V-0
- Meets and exceeds ANSI/TIA-568-C.2, ISO/IEC 11801 and EN 50173-1 specifications

- Dual-type IDC headers, situated 180 relative to the RJ45 ports, terminated using 110-type punch tool
- Color coded for both T568A and T568B installations

Special Notes / Requirements

Warranty	2 Years
Note	IDC Contact: 0.8mm thickness alloy, tin plating over nickel Jack Contact: phosphor bronze, gold over nickel

Environmental

Operating Temperature	-10~50
Humidity	10~65%

Physical Characteristics

Color	Black
Product Length	19.0 in [48.2 cm]
Weight of Product	14.4 oz [409 g]

Packaging Information

Package Length	19.3 in [49 cm]
Package Width	2.2 in [57 mm]
Package Height	1.9 in [47 mm]
Shipping (Package) Weight	17.4 oz [494 g]

What's in the Box

Included in Package	24 Port 1/2U Rackmount Cat5e 110 Patch Panel
	M6 Screws
	M5 Screws
	Zip Ties
	Instruction Manual



****Product appearance and specifications are subject to change without notice.***

