

100Mbps Full/Low Profile Ethernet Multi Mode SC Fiber PCI NIC Card 2km

Produkt ID: PCI100MMSC



The PCI100MMSC 100 Mbps Fiber Optic (MM SC) PCI Ethernet Adapter Card offers the perfect "Fiber-to-the-desk" solution allowing you to add a multimode SC fiber port to your system through an available standard or low-profile PCI slot.

A simple solution for connecting a computer directly to a fiber network, the Fiber Ethernet Adapter card can be installed in the computer through any PCI slot and is perfectly suited for high bandwidth applications with support for Full Duplex operation and 10/100 Mbps transfer speeds at distances of up to 2km.

Application Diagrams: Installing the PCI100MMSC is a simple upgrade

Ideal for secure network setups, the PCI100MMSC offers a direct fiber connection which is not susceptible to electronic interference like standard RJ45 networks.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Add a 10/100 Mbps SC Fiber connection to a PCI compatible PC
- Add network connectivity to a PC up to 2km Away
- Create a secure connection between the PC and a fiber switch

- Perfect for remote embedded industrial monitoring systems, and high speed video surveillance

Funktioner

- Compliant with PCI rev. 2.1 standards
- Advanced Configuration Power Management Interface (ACPI) 1.0
- Supports PCI Bus Power Managements Interface Ver. 1.0/1.1 and Network Device Class Power Managements Ver. 1.0a
- Supports PC99, PC2001, and NET PC requirements
- VLAN Management
- Optical Wavelength of 1310nm
- Maximum fiber distance up to 2km
- Wake on LAN support
- Connection diagnostic utilities
- WHQL drivers

Hårdvara

Garantipolicy	2 Years
Portar	1
Gränssnitt	Fiber Ethernet
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil (inkl. LP-fäste)
Industristandarder	IEEE802.3u, 100Base-FX, IEEE802.3x, IEEE802.1Q, IEEE802.1p
Chipset-ID	VIA/VLI - VT6105M

Prestanda

Buffertstorlek	2 KB
Kompatibla nätverk	100 Mbps



Stöd för full-duplex Ja

Kontakt(er)

Kontakttyp(er) PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)

Externa portar Fiberoptisk SC duplex

Mjukvara

OS-kompatibilitet Windows® 2000, XP, Vista, 7, 8, 8.1, 10, 11
Windows Server® 2003, 2008 R2, 2012
Linux 3.5.x to 4.4.x <i>LTS Versions only</i>

Indikatorer

LED-indikatorer Green - Link
Green - Activity

Ström

Strömförbrukning 1W

Miljö

Drifttemperatur 0°C to 45°C (32°F to 113°F)
Förvaringstemperatur -10°C to 70°C (14°F to 158°F)
Luftfuktighet 5~95% RH

Utseende

Produktlängd 4.8 in [12.1 cm]
Produktbredd 2.2 in [56 mm]
Produkthöjd 0.7 in [18 mm]
Produktvikt 2.8 oz [80 g]

Förpackning

Package Length 8.4 in [21.3 cm]
Package Width 2.0 in [50 mm]
Package Height 6.9 in [17.5 cm]



Fraktvikt (förpackning) 7.1 oz [200 g]

Vad det är i lådan

Ingår i paketet	PCI to SC 10/100 Fiber NIC
	Low profile bracket
	Driver CD
	Instruction Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.

