

PCI Wireless N Card - 150Mbps 802.11b/g/n Network Adapter Card – 1T1R 2dBi

Produkt ID: PCI150WN1X1



The PCI150WN1X1 PCI Wireless N card lets you add high speed 802.11n network connectivity to almost any PCI-enabled desktop/workstation PC. Using a 1T1R (1 Transmitter, 1 Receiver) design over the 2.4GHz frequency, the card supports data rates up to 150Mbps.

Providing a versatile wireless solution, this WiFi N adapter offers support for standard and advanced security options such as WEP, WPA and WPA2. Also included are Quality of Service (QoS) supports for traffic management, quick and easy device connection through WiFi Protected Setup (WPS) and backward compatibility with 802.11b/g networks (11/54Mbps).

For flexible installation options, the card comes equipped with a standard profile bracket and includes a low-profile/half-height bracket suitable for installation in a small form factor PC.

Backed by a StarTech.com 2-year warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet



Användning

- Replace or upgrade the wireless capabilities of a desktop computer
- Connect a remote workstation PC to a wireless-N network, in environments where running network cables is not feasible

Funktioner

- 1 Transmitter/ 1 Receiver (1x1:1) antenna configuration
- IEEE 802.11n compliant, with support for wireless data rates of up to 150Mbps
- Backward compatible with IEEE 802.11b/g standards for up to 11/54Mbps connections respectively with Wireless-B and Wireless-G networks
- Supports WEP (64-128-bit), WPA and WPA2 security
- Support for WMM/WMM-PS Quality of Service (QoS)
- Infrastructure, Ad-Hoc and Soft AP network mode support
- Detachable 2dBi antenna
- Includes Low Profile/Half-Height installation bracket

Hårdvara

Garantipolicy	2 Years
Gränssnitt	Trådlöst Ethernet
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil (inkl. LP-fäste)
Antennkonfiguration	1x1:1(TxR:S)
Chipset-ID	Ralink - RT3060F

Prestanda

Maximal dataöverföringshastighet	150 Mbps
Bandbredd	20/40 MHz
Frekvensområde	2.4 GHz~2.484 GHz
Säkerhetsfunktioner	WEP-datakryptering

	Stödda protokoll	WPA-datakryptering TKIP/AES CSMA/CA
Kontakt(er)	Kontakttyp(er)	1 - PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
	Externa portar	1 - RP-SMA (Koaxial, Reverse Polarity SubMiniature A)
Mjukvara	OS-kompatibilitet	Windows® XP, Vista, 7, 8, 8.1 Windows Server® 2003, 2008 R2 Linux 3.5.x to 4.4.x LTS Versions only
Särskilda anmärkningar/krav		
	System- och kabelkrav	Available PCI expansion card slot
Miljö	Drifttemperatur	0°C to 55°C (32°F to 131°F)
	Förvaringstemperatur	-20°C to 70°C (-4°F to 158°F)
	Luftfuktighet	10~90% RH
Utseende	Produktlängd	5.1 in [12.9 cm]
	Produktbredd	0.7 in [1.8 cm]
	Produkthöjd	3.9 in [9.9 cm]
	Produktvikt	1.6 oz [45 g]
Förpackning		
	Förpackningsantal	1
	Paketets längd	6.4 in [16.3 cm]
	Paketets bredd	5.4 in [13.6 cm]

Paketets höjd 1.3 in [32 mm]

Fraktvikt (förpackning) 5.3 oz [150 g]

Vad det är i lådan

Ingår i paketet	1 - PCI Wireless Card
	1 - 2dBi Antenna
	1 - Low Profile Bracket
	1 - Driver CD
	1 - Instruction Manual

Warranty
Information

Warranty	2 År
----------	------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.