

1 Port PCI Parallel Adapter Card

Produkt ID: PCI1P2



The PCI1P2 1-Port Parallel PCI Card adds one ECP/EPP/SPP/BPP IEEE 1284 port to your PC, with support for data transfer speeds of up to 1.8Mbps.

This versatile card offers compatibility with PCI or PCI-X expansion slots (3.3/5V, 32/64-bit), as well as a simple plug and play installation with support and drivers for a broad range of operating systems including Windows® 7, Server 2008 R2, XP Embedded DOS®, Linux® and more. The PCI Parallel card also features IRQ sharing and hot swapping capabilities, which guarantee convenient, hassle-free connections to any parallel peripheral.

This product is a replacement for our PCI1P card.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifikat, rapporter och kompatibilitet

Användning

- Connecting any parallel peripheral including printers, scanners, CD-R/RWs, Zip® drives, and memory card readers to a computer, through PCI/PCI-X

Funktioner

- Supports EPP, ECP, SPP and BPP
- Data transfer rates of up to 1.8Mbps

- Supports both 64-bit PCI-X & 32-bit PCI slots
- Easy plug and play installation with I/O address and IRQ assigned by system
- Support for Microsoft Windows®, Linux, and DOS

Hårdvara

Garantipolicy	Lifetime
Portar	1
Gränssnitt	Parallell
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil
Porttyp	Inbyggd på kort
Rättsliga godkännanden	EN55022 Class B, EN55024, EN61000-3-2, EN61000-3-3, FCC Part 15 Class B, RoHS
Industristandarder	IEEE-1284, PCI Ver 3.0, 2.3, 2.2, 2.1
Chipset-ID	Sunix - SUN1989

Prestanda

Maximal dataöverföringshastighet	1.8Mbps
FIFO	16 Byte
Stödda protokoll	BPP, ECP, EPP, SPP

Kontakt(er)

Kontakttyp(er)	PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
Externa portar	DB-25 (25-stifts, D-Sub)

Mjukvara

OS-kompatibilitet	Windows® DOS, 95, 98SE, NT, ME, XP Embedded, POS Ready 2009, Embedded System 2009, XP, Vista, 7, 8, 8.1 Windows Server® 2000, 2003, 2008 R2, 2012, 2012 R2
-------------------	---

Linux 2.4.x / 2.6.x

Microsoft
WHQL-certifierad Ja

Särskilda
anmärkningar/krav

System- och kabelkrav PC with an available PCI/PCI-X slot

Miljö

Drifttemperatur 0°C to 60°C (32°F to 140°F)
Förvaringstemperatur -20°C to 85°C (-4°F to 185°F)
Luftfuktighet 5~95% RH

Utseende

Produktlängd 4.8 in [12.1 cm]
Produktbredd 0.6 in [14 mm]
Produkt höjd 2.5 in [63 mm]
Produktvikt 1.7 oz [48 g]

Förpackning

Package Length 6.7 in [17 cm]
Package Width 5.5 in [14 cm]
Package Height 1.3 in [32 mm]
Fraktvikt (förpackning) 4.9 oz [140 g]

Vad det är i lådan

Ingår i paketet PCI Parallel Card
Driver CD
User Manual

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.