

## 2 Port PCI Parallel Adapter Card - EPP/ECP

**Product ID:** PCI2PECP



The PCI2PECP 2 Port EPP/ECP PCI Parallel Adapter Card can be installed in an available PCI slot, adding two IEEE 1284 ports to your PC and supporting data transfer speeds of up to 1.5 Mbps (up to 3 times faster than built-in parallel ports).

Installing the EPP/ECP parallel adapter card is easy, with support for Windows 8, 7, Vista, XP, ME, 98SE, 95, DOS, Windows Server 2012, and Linux. Plus, IRQ sharing and plug and play capabilities guarantee convenient, hassle-free connections to any parallel peripheral.

A complete dual profile solution, this parallel adapter card provides both a standard bracket and a low-profile/half-height bracket for adapting to slimline or small form factor system applications.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

## Certifications, Reports and Compatibility

### Applications

- Connects any parallel peripheral including printers, scanners, CD-R/RWs, Zip drives, and memory card readers

### Features

- Easy plug and play installation
- Data transfer rates of up to 1.5 Mbps
- Compatible with Linux and all versions of Windows including Windows XP

- IRQ sharing eliminates conflicts between multiple cards
- Supports EPP, ECP, SPP and BPP
- Installation scripts available for Linux RedHat 7.2, SuSE 7.3 and Mandrake 8.2
- Includes half-height/low profile mounting bracket

---

#### Hardware

Warranty	Lifetime
Ports	2
Interface	Parallel
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Industry Standards	IEEE-1284
Chipset ID	ASIX - MCS9815CV

---

#### Performance

Maximum Data Transfer Rate	1.5 Mbps
Supported Protocols	EPP, ECP, SPP, BPP, PS2

---

#### Connector(s)

Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
External Ports	DB-25 (25 pin, D-Sub)

---

#### Software

OS Compatibility	Windows DOS, 95, 98SE, ME, XP, Vista, 7, 8, 8.1, 10 Windows Server 2003, 2008 R2, 2012 Linux 3.5.x to 4.11.x <i>LTS Versions only</i>
------------------	---

---

#### Special Notes / Requirements

System and Cable Requirements	Unused PCI slot
-------------------------------	-----------------

---

**Physical Characteristics**

Material	Steel
Product Length	4.7 in [12 cm]
Product Width	0.8 in [20 mm]
Product Height	4.7 in [12 cm]
Weight of Product	2.5 oz [70 g]

---

**Packaging Information**

Package Length	8.3 in [21 cm]
Package Width	1.7 in [42 mm]
Package Height	5.7 in [14.4 cm]
Shipping (Package) Weight	7.4 oz [210 g]

---

**What's in the Box**

Included in Package	2 Port PCI Parallel Card
	Ribbon Cable w/DB25F Plate
	Driver CD
	Instruction Manual
	Low Profile Brackets

---

***\*Product appearance and specifications are subject to change without notice.***

