

2 Port 16C550 Serial and 1 Port EPP/ECP Parallel Slot Saver PCI Card

Product ID: PCI2S1PVA



The PCI2S1PVA 2 Port 16C550 Serial and 1 Port EPP/ECP Parallel Slot Saver PCI Card gives you two 16C550 serial ports with data transfer speeds up to 460.8Kbps on the card, and one EPP/ECP parallel port with data transfer speeds up to 1.5Mbps (Up to 3x faster than onboard parallel ports) on a separate riser.

Perfect for connecting to any parallel and serial devices including printers, scanners and ISDN terminal adapters. Installation is a breeze with support for a broad range of operating systems including Windows, Mac OS and Linux. Plus, IRQ sharing and a PCI plug and play interface, guarantee convenient, hassle-free connections to your serial and parallel peripherals.

Backed by a StarTech.com lifetime warranty and free lifetime technical support.

Certifications, Reports and Compatibility

Applications

- Connect parallel and serial devices like printers, scanners, ISDN terminal adapters, CD-R/RWs, Zip drives and memory card readers

Features

- Large list of supported operating systems including Windows, Mac OS and Linux
- Two 16C550 serial ports with data transfer up to 460.8 Kbits/sec
- One EPP/ECP parallel port with data transfer up to 1.5 Mbits/sec
- Parallel port supports EPP, ECP, SPP and BPP

- IRQ sharing eliminates conflicts between multiple cards

Hardware

Warranty	Lifetime
Ports	3
Interface	Serial Parallel
Bus Type	PCI / PCI-X (5 / 3.3V)
Card Type	Standard Profile (LP bracket incl.)
Port Style	Integrated on Card
Chipset ID	ASIX - MCS9835CV

Performance

Maximum Data Transfer Rate	Serial - 460.8Kbps Parallel - 1.5Mbps
Serial Protocol	RS-232
Max Baud Rate	460.8 Kbps
Data Bits	5, 6, 7, 8
FIFO	Serial: 32 Bytes Parallel: 16-Bytes
Parity	Even, Odd, Force or None

Connector(s)

Connector Type(s)	PCI / PCI-X (Universal 3.3 & 5V, 32-bit)
External Ports	DB-25 (25 pin, D-Sub) DB-9 (9 pin, D-Sub)

Software

OS Compatibility	Windows 8 (32/64bit), 7 (32/64), Vista(32/64), XP(32/64), XP Embedded, POS Ready 2009, Embedded System 2009, CE 5.0/6.0, 2000, 98SE, 95, DOS
------------------	--



Windows Server 2012, 2008 R2, 2003(32/64)

Mac OS 10.4 and up (Tested up to 10.9)

Linux

Environmental

Operating Temperature	-10C to 80C (14F to 176F)
Storage Temperature	-20C to 100C (-4F to 212F)
Humidity	5~85% RH

Physical Characteristics

Product Length	4.7 in [12 cm]
Product Height	2.2 in [55 mm]

Packaging Information

Package Length	8.3 in [21 cm]
Package Width	1.6 in [40 mm]
Package Height	5.7 in [14.5 cm]
Shipping (Package) Weight	7.8 oz [220 g]

What's in the Box

Included in Package	PCI 2S1P Card
	Low Profile Brackets
	Ribbon Cable
	Driver CD
	User Manual

****Product appearance and specifications are subject to change without notice.***

