

4 Port PCI High Speed USB 2.0 Adapter Card

Produkt ID: PCI330USB2



StarTech.com's 4-Port PCI USB 2.0 Adapter Card adds three external USB 2.0 ports as well as one internal USB 2.0 port, through simple installation in a single PCI slot.

The PCI USB 2.0 card supports plug and play installation as well as hot-swappable connectivity with USB 2.0 devices, ensuring convenient, hassle-free connections without having to reboot the computer.

The 4-port PCI USB 2.0 adapter card is built with an NEC chipset for increased reliability and compatibility with USB devices., and supports hot swappable connections with USB devices for convenient, hassle free device installation without having to reboot the host computer.

A high quality, highly dependable solution, the PCI USB 2.0 adapter card is backed by StarTech.com's Lifetime Warranty and FREE LIFETIME tech support.

Certifikat, rapporter och kompatibilitet



Användning

- Expand a PCI-based system's USB capabilities with four additional usable USB ports

- Add additional USB bandwidth to a system that already uses many USB devices/hubs
- Connect additional external hard drives, CD/DVD drives, MP3 players, printers, scanners, webcams, game controllers, digital cameras, etc. to a computer system

Funktioner

- 3 external USB 2.0 ports
- A shared port between an external mini-B/internal type A/internal header
- Compliant with USB 2.0 specifications, which supports transfer rates up to 480 Mbps
- Backwards compatible with USB 1.0/1.1 devices
- Compliant with PCI revision 2.2 specification
- Supports up to 127 USB devices per port (requires additional USB hubs)
- Plug-and-Play and Hot-Swap compatible

Hårdvara

Garantipolicy	Lifetime
Portar	4
Gränssnitt	USB 2.0
Busstyp	PCI / PCI-X (5 / 3.3V)
Korttyp	Standardprofil
Chipset-ID	Renesas/NEC - D720102GC

Prestanda

Maximal dataöverföringshastighet	480 Mbps
----------------------------------	----------

Kontakt(er)

Kontakttyp(er)	1 - PCI/PCI-X (universell 3,3 & 5 V, 32-bitars)
Interna portar	1 - USB 2.0 Type-A (4 stift, 480 Mbps)
Externa portar	3 - USB 2.0 Type-A (4 stift, 480 Mbps)

1 - USB Mini-B (5-stifts)

Mjukvara

OS-kompatibilitet	Windows 98SE/ ME/ 2000/ XP (32/64-bit)/ Server 2008 R2/ Vista (32/64-bit)/ 7 (32/64-bit)/ 8 (32/64-bit) , Mac OS X (tested up to 10.4), Linux
-------------------	---

Särskilda anmärkningar/krav

System- och kabelkrav	Available PCI expansion slot
-----------------------	------------------------------

Utseende

Produktlängd	5.0 in [12.7 cm]
Produktbredd	4.7 in [12 cm]
Produkthöjd	0.8 in [2 cm]
Produktvikt	1.6 oz [45 g]

Förpackning

Paketets längd	6.8 in [17.2 cm]
Paketets bredd	2.6 in [65 mm]
Paketets höjd	7.1 in [18.1 cm]
Fraktvikt (förpackning)	0.2 lb [0.1 kg]

Vad det är i lådan

Ingår i paketet	1 - PCI USB 2.0 Card
	1 - Driver CD
	1 - Instruction Manual

Warranty Information

Warranty	Livslängd
----------	-----------

* Produkters utseende och specifikationer kan komma att ändras utan förvarning.